



ミヤコ株式会社の
商標登録マークです。

ソロバン玉リング式銅管用継手

ソロバン玉リング入片ネジエルボ

M148RKG MB



寸法(×R)	d	L	H	価格	入数
3 × 1/8	3.2	20	26	700	20
4 × 1/8	4.2	20	26	670	20
5 × 1/8	5.2	20	26	670	20
6 × 1/8	6.2	20	26	670	20
6 × 1/4	6.2	24	30	810	20
6 × 3/8	6.2	27	33	1,080	20
6 × 1/2	6.2	32	34	2,000	20
6.35 × 1/8	6.55	22	30	880	20
6.35 × 1/4	6.55	24	30	810	20
6.35 × 3/8	6.55	27	33	1,080	20
6.35 × 1/2	6.55	32	34	2,000	20
8 × 1/8	8.2	21	30	880	20
8 × 1/4	8.2	24	30	810	20
8 × 3/8	8.2	27	33	1,080	20
8 × 1/2	8.2	32	35	2,000	20
9.52 × 1/4	9.7	26	35	1,180	20

◎材質：黄銅製

寸法(×R)	d	L	H	価格	入数
9.52 × 3/8	9.7	27	35	1,080	20
9.52 × 1/2	9.7	32	39	2,000	20
10 × 1/8	10.2	25	35	1,180	20
10 × 1/4	10.2	26	35	1,180	20
10 × 3/8	10.2	27	35	1,080	20
10 × 1/2	10.2	32	39	2,000	20
12 × 1/4	12.2	30	43	2,000	20
12 × 3/8	12.2	32	44	2,000	20
12 × 1/2	12.2	32	44	1,960	20
12.7 × 3/8	12.9	32	44	1,960	20
12.7 × 1/2	12.9	32	44	1,960	20
15 × 1/2	15.2	37	50	6,280	10
15.88 × 1/2	16.1	37	50	8,500	10
15.88 × 3/4	16.1	42	59	9,300	10
19.05 × 3/4	19.25	44	59	9,300	10
22.22 × 3/4	22.5	44	54	12,800	5

ソロバン玉リング入エルボ

M148RK MB



寸法	d	L	H	価格	入数
6 × 6	6.2	31	31	1,080	50
6.35 × 6.35	6.55	31	31	1,080	50
8 × 8	8.2	31	31	1,080	50
9.52 × 9.52	9.7	35	35	1,500	25
10 × 10	10.2	35	35	1,500	25
12 × 12	12.2	43	43	2,420	15
12.7 × 12.7	12.9	44	44	2,420	15
15 × 15	15.2	50	50	8,000	10
15.88 × 15.88	16.1	50	50	8,000	10
19.05 × 19.05	19.25	60	60	12,800	5
22.22 × 22.22	22.5	54	54	16,800	5

◎材質：黄銅製

ソロバン玉ナット

M614RK MB



※6A・6Bをご注文の際はあらかじめ製品図面を参照の上平配して下さい。

寸法	d	d _h	L	価格	入数
3	G _{1/8}	3.2	10	130	20
4	G _{1/8}	4.2	10	130	20
5	G _{1/8}	5.2	10	130	20
6A	G _{1/8}	6.2	10	130	20
6B	G _{1/8}	6.2	13	130	20
6.35	G _{1/4}	6.55	13	160	20
8	G _{1/4}	8.2	13	160	20
9.52	G _{3/8}	9.7	16	260	20
10	G _{3/8}	10.2	16	260	20
12	G _{1/2}	12.2	18	370	20
12.7	G _{1/2}	12.9	18	370	20
15	G _{5/8}	15.2	20	740	20
15.88	G _{5/8}	16.1	20	740	10
19.05	G _{3/4}	19.25	23	910	10
22.22	G _{3/4}	22.5	23	2,100	10

◎材質：黄銅製

ソロバン玉リング

M614RK-R MB



寸法	d	D	L	価格	入数
3	3.2	5.5	5	44	20
4	4.2	6.3	5.5	44	20
5	5.2	7.5	5.5	44	20
6A	6.2	8.3	5.5	40	20
6B	6.2	9	7.5	40	20
6.35	6.55	9	6.5	40	20
8	8.2	11	7.5	40	20
9.52	9.7	13	9	76	20
10	10.2	13.5	9	76	20
12	12.2	15.5	11	120	20
12.7	12.9	16	10	120	20
15	15.2	19	12	260	10
15.88	16.1	20	12	260	10
19.05	19.25	24	13.5	300	10
22.22	22.5	26	11	530	10

◎材質：黄銅製

※6A・6Bをご注文の際はあらかじめ製品図面を参照の上平配して下さい。

軟質銅管用スリーブ

M154RK-S MB



寸法	d	価格	入数
9.52	8.15	240	50
12.7	11.25	270	50
15.88	14.3	290	50
22.22	20.4	640	50

◎材質：黄銅製

※Mタイプ：コイル巻(ナサン巻管)用。
Kタイプ、Lタイプには使用できません。

銅管サイズ適合表

呼び径	外径	肉厚
1/4	φ 9.52	0.64
3/8	φ 12.7	0.64
1/2	φ 15.88	0.71
3/4	φ 22.22	0.81