



39-00-0107	2759PBT	バラ状 LOOSE	0.00091 MIN REFLOWED TIN	
39-00-0064	PBT	連鎖状 CHAIN		リン 青銅 PHOS BRO.
39-00-0381	PBGL	バラ状 LOOSE	SELECTIVE GOLD: 0.00038 MIN. OVERALL GOLD FLASH: 0.00005-0.00025 OVERALL NICKEL UNDERPLATE: 0.00076 MIN.	
39-00-0380	PBG	連鎖状 CHAIN		
39-00-0377	GL	バラ状 LOOSE	SELECTIVE GOLD: 0.00038 MIN. OVERALL GOLD FLASH: 0.00005-0.00025 OVERALL NICKEL UNDERPLATE: 0.00076 MIN.	黄銅 BRASS
39-00-0376	G	連鎖状 CHAIN		
39-00-0374	GS	連鎖状 CHAIN		
39-00-0373	TL	バラ状 LOOSE	0.00089 MIN REFLOWED TIN OVER 0.00051 MIN COPPER UNDERPLATE	
39-00-0372	2759 T	連鎖状 CHAIN		
EDP.NO.	ENG.NO.	端子形状 FORM	メッキ仕様 FINISH	材質 MATL

NOTES:

1. MATERIAL: SEE CHART
2. FINISH: SEE CHART
3. PRODUCT SPECIFICATION PS-10-07
4. 芯ズレ 0.13最大
DIM 1.98±0.25 TO BE SYMMETRICAL
WITHIN 0.13 T.I.R
5. THIS PART CONFORMS TO CLASS B REQUIREMENTS OF
COSMETIC SPECIFICATION PS-45499-002

ADD/REMOVE PARTS EC NO: UCP2012-2836 DRAWN: MSTRÖH 2012/01/05 CHKD: J.BELL 2012/01/05 APPR: F.SMITH 2013/05/13	DESCRIPTION REV	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION		
		▽=0	mm	INCH	MM ONLY		METRIC	TITLE			
		▽=0	4 PLACES ±	---	±	---	DRAWN BY	DATE	MINI, KK, CRIMP TYPE TERM		
		▽=0	3 PLACES ±	---	±	---	CHECKED BY	DATE	MATERIAL NO.		
			2 PLACES ±	---	±	---	2000/03/28	DOCUMENT NO.			
			1 PLACE ±	---	±	---	2002/04/08	SEE CHART			
			0 PLACE ±	---	±	---		SD-2759*			
			ANGULAR ±		---	---		SHEET NO.			
			DRAFT WHERE APPLICABLE		MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		1 OF 1		