



■ 止まり穴用ストレートフルートヘッド

中心部内部給油式

(mm)

DC	呼 び 記 号	在庫	刃数	LH	CRKS	図	対応ホルダ
		RP1010					
14	RX1S14000H7DSTP1	●	6	17.9	TP1	1	RX1SX○○S16ATP1
15	RX1S15000H7DSTP1	●	6	17.9	TP1	1	RX1SX○○S16ATP1
16	RX1S16000H7DSTP2	●	6	17.9	TP2	1	RX1SX○○S20ATP2
17	RX1S17000H7DSTP2	●	6	17.9	TP2	1	RX1SX○○S20ATP2
18	RX1S18000H7DSTP3	●	6	17.9	TP3	1	RX1SX○○S20ATP3
19	RX1S19000H7DSTP3	●	6	17.9	TP3	1	RX1SX○○S20ATP3
20	RX1S20000H7DSTP4	●	6	17.9	TP4	1	RX1SX○○S20ATP4
21	RX1S21000H7DSTP4	●	6	17.9	TP4	1	RX1SX○○S20ATP4
22	RX1S22000H7DSTP4	●	6	17.9	TP4	1	RX1SX○○S20ATP4
23	RX1S23000H7DSTP5	●	6	18.9	TP5	1	RX1SX○○S20ATP5
24	RX1S24000H7DSTP5	●	6	18.9	TP5	1	RX1SX○○S20ATP5
25	RX1S25000H7DSTP5	●	8	18.9	TP5	1	RX1SX○○S20ATP5
26	RX1S26000H7DSTP5	●	8	18.9	TP5	1	RX1SX○○S20ATP5
27	RX1S27000H7DSTP5	●	8	18.9	TP5	1	RX1SX○○S20ATP5
28	RX1S28000H7DSTP6	●	8	18.9	TP6	1	RX1SX○○S25ATP6
29	RX1S29000H7DSTP6	●	8	18.9	TP6	1	RX1SX○○S25ATP6

注1) ヘッドとホルダは取付けねじサイズCRKSが同じものをご使用ください。