







●：安定切削（第一推奨） ●：一般切削（第一推奨） ✖：不安定切削（第一推奨）
○：安定切削（第二推奨） ○：一般切削（第二推奨） ⚡：不安定切削（第二推奨）

被削材	材料		コーティング																	コーティング	サーメット	超硬合金																																							
	P	M	MS6015	MC6115	MC6125	MC6015	UE6105	UE6110	UE6020	MS7025	MC7015	MC7025	MP7035	US7020	US735	MC5115	MC5125	MC5005	MC5015	UC5105	UC5115	MS9025	MP9005	MP9015	MP9025	VP10RT	VP15TF	VP30RT	UP20M	MP3025	AP25N	VP25N	VP45N	NX2525	NX3035	MT9005	RT9010	UT120T	HT105T	HT10	TF15																				
AZ  中切削～ 仕上げ切削	CCGT060202-AZ	0.2																																																											
	CCGT060204-AZ	0.4																																																											
	CCGT09T302-AZ	0.2																																																											
	CCGT09T304-AZ	0.4																																																											
	CCGT09T308-AZ	0.8																																																											
R/L-F  仕上げ切削	CCGT04T0V3L-F	0.03																																																											
	CCGT04T001L-F	0.1																																																											
	CCGT04T002L-F	0.2																																																											
	CCGT04T004L-F	0.4																																																											
	CCGT04T001MR-F	0.1*	●																																																										
	CCGT04T001ML-F	0.1*	●																																																										
	CCGT04T002MR-F	0.2*	●																																																										
	CCGT04T002ML-F	0.2*	●																																																										
CCGT04T004MR-F	0.4*	●																																																											
CCGT04T004ML-F	0.4*	●																																																											
R/L-F  仕上げ切削	CCGH060202R-F	0.2																																																											
	CCGH060202L-F	0.2																																																											
	CCGH060204R-F	0.4																																																											
	CCGH060204L-F	0.4																																																											
	CCGH060202MR-F	0.2*	●																																																										
	CCGH060202ML-F	0.2*	●																																																										
	CCGH060204MR-F	0.4*	●																																																										
CCGH060204ML-F	0.4*	●																																																											
LP  軽切削	CCMT060202-LP	0.2		●																																																									
	CCMT060204-LP	0.4	●	●	▲	▲	▲																								●					●																									
	CCMT060208-LP	0.8	●	●	▲	▲	▲																																																						
	CCMT09T304-LP	0.4	●	●	▲	▲	▲																																																						
	CCMT09T308-LP	0.8	●	●	▲	▲	▲																																																						
LM  軽切削	CCMT060202-LM	0.2								●	●																																																		
	CCMT060204-LM	0.4								●	●	●																●																																	
	CCMT060208-LM	0.8								●	●	●															●																																		
	CCMT09T302-LM	0.2								●	●																																																		
	CCMT09T304-LM	0.4								●	●	●																	●																																
CCMT09T308-LM	0.8								●	●	●																●																																		
LS  軽切削	CCMT060202-LS	0.2																											●																																
	CCMT060204-LS	0.4																											●																																
	CCMT09T302-LS	0.2																												●																															
	CCMT09T304-LS	0.4																												●																															
	CCMT09T308-LS	0.8																												●																															

* RE値は最大値を示します。

● = NEW

