








●: 安定切削 (第一推奨)   ●: 一般切削 (第一推奨)   ✳: 不安定切削 (第一推奨)  
○: 安定切削 (第二推奨)   ○: 一般切削 (第二推奨)   ✳: 不安定切削 (第二推奨)

被削材	P 鋼	M ステンレス鋼	K 鋳鉄	N 非鉄金属	S 耐熱合金、チタン合金	コーティング																コート サーメット	サーメット	超硬合金																								
	○	○	●	○	●	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○																							
インサート 外観	呼 び 記 号	RE (mm)	UE6105	UE6110	UE6020 <small>NEW</small> MC6115	MC6125	MC6015	MC6025	MC6035	UH6400	MS6015	MC7015	MC7025	MP7035	US7020	US735	MC5005	MC5015	UC5105	UC5115	MH515	MV9005 <small>*1</small>	MP9005	MP9015	MP9025	US905	VP05RT	VP10RT	VP15TF	UP20M	MP3025	AP25N	VP25N	NX2525	NX3035	UT120T	HT105T	HT110	RT9010	MT9015								
 中切削	WNMG060404-GK	0.4																▲▲																														
	WNMG060408-GK	0.8																▲▲																														
	WNMG080404-GK	0.4																▲▲																														
	WNMG080408-GK	0.8																▲▲																														
	WNMG080412-GK	1.2																▲▲																														
 中切削	WNMG060404-GM	0.4										●●●																																				
	WNMG060408-GM	0.8										●●●																																				
	WNMG080404-GM	0.4										●●●																																				
	WNMG080408-GM	0.8										●●●																																				
	WNMG080412-GM	1.2										●●●																																				
 中切削	WNMG06T304-MA	0.4	▲▲														●																															
	WNMG06T308-MA	0.8	▲▲														●																															
	WNMG06T312-MA	1.2	▲▲														●																															
	WNMG060404-MA	0.4	▲▲				▲▲										●																															
	WNMG060408-MA	0.8	▲▲				▲▲					●●					▲▲											●																				
	WNMG060412-MA	1.2	▲▲				▲▲					●●					▲▲										●																					
	WNMG080404-MA	0.4	▲▲▲●●			▲▲						●●▲▲					▲▲							●●		●													●									
WNMG080408-MA	0.8	▲▲▲●●			▲▲▲▲						●●▲▲					▲▲▲▲							●●		●												●											
WNMG080412-MA	1.2	▲▲▲●●			▲▲▲▲						●●▲▲					▲▲▲▲							●●		●													●										
WNMG080416-MA	1.6	▲▲		●●																			●●		●																							
WNMG100612-MA	1.2		▲																																													
 中切削	WNMG080404-MH	0.4	▲▲▲●●			▲▲																																										
	WNMG080408-MH	0.8	▲▲▲●●			▲▲▲▲																																										
	WNMG080412-MH	1.2	▲▲▲●●			▲▲▲▲																	▲																									
 中切削	WNMG080404	0.4	▲▲▲●●			▲▲											▲▲									●										●												
	WNMG080408	0.8	▲▲▲●●			▲▲▲▲											▲▲									●			●								●											
	WNMG080412	1.2	▲▲▲●●			▲▲▲▲											▲▲									●														●								
	WNMG080416	1.6																	▲																													
 中切削 (ワイパー)	WNMG060408-MW	0.8	▲▲▲			▲▲											▲▲▲▲																															
	WNMG060412-MW	1.2	▲▲			▲▲											▲▲▲																															
	WNMG080408-MW	0.8	▲▲▲●●			▲▲											▲▲▲▲																															
	WNMG080412-MW	1.2	▲▲			●●▲▲											▲▲▲▲																															
 荒切削	WNMG080408-RP	0.8	▲▲			●●▲▲▲▲																																										
	WNMG080412-RP	1.2	▲▲			●●▲▲▲▲																																										

\*1 MV9005は日本限定販売材種です。 ● = **NEW**  
\*2 MWプレーカ(ワイパーインサート)はA028ページを参照の上、ご使用ください。

A  
旋削用インサート  
ネガ  
穴つき  
C  
D  
R  
S  
T  
V  
W