

旋削用CBNインサート[ネガ]



CBN

B

CBNインサート

ネガ

穴つき

C

D

R

S

T

V

W

被削材	H	高硬度材										切削状態(目安) :							
	K	鋳鉄										● : 安定切削 ● : 一般切削 ✳ : 不安定切削							
インサート 外観	S	耐熱合金、チタン合金										ホーニング(呼び記号末尾) : B009ページをご参照ください。							
		焼結合金																	
呼び記号	コーテッド CBN					CBN					ソリッド CBN	寸法 (mm)					形状		
	NEW BC8210	BC8220	BC8105	BC8110	NEW BC8130	NEW BC5110	MB8110	MB8120	MB8130	MB4120	MB710	MB730	MBS140	IC	S	RE		LE	D1
ニューブチカット	NP-CNGA120404FS4	●	●	▲	▲		●							12.7	4.76	0.4	1.8	5.16	
	NP-CNGA120408FS4	●	●	▲	▲		●							12.7	4.76	0.8	2.0	5.16	
	NP-CNGA120412FS4	●	●	▲	▲		●							12.7	4.76	1.2	2.2	5.16	
	NP-CNGA120404GS4	●	●	▲										12.7	4.76	0.4	1.8	5.16	
	NP-CNGA120408GS4	●	●	▲										12.7	4.76	0.8	2.0	5.16	
	NP-CNGA120412GS4	●	●	▲										12.7	4.76	1.2	2.2	5.16	
	NP-CNGA120404GA4	●	●	▲	●		●							12.7	4.76	0.4	1.8	5.16	
	NP-CNGA120408GA4	●	●	▲	●		●							12.7	4.76	0.8	2.0	5.16	
	NP-CNGA120412GA4	●	●	▲	●		●							12.7	4.76	1.2	2.2	5.16	
	NP-CNGA120404GH4	●	●	▲	▲	●								12.7	4.76	0.4	1.8	5.16	
	NP-CNGA120408GH4	●	●	▲	▲	●								12.7	4.76	0.8	2.0	5.16	
	NP-CNGA120412GH4	●	●	▲	▲	●								12.7	4.76	1.2	2.2	5.16	
	NEW NP-CNGA120404VA4	●	●	▲										12.7	4.76	0.4	1.8	5.16	
	NEW NP-CNGA120408VA4	●	●	▲										12.7	4.76	0.8	2.0	5.16	
	NEW NP-CNGA120412VA4	●	●	▲										12.7	4.76	1.2	2.2	5.16	
	NP-CNGA120404TS4	●	●	▲										12.7	4.76	0.4	1.8	5.16	
	NP-CNGA120408TS4	●	●	▲										12.7	4.76	0.8	2.0	5.16	
	NP-CNGA120412TS4	●	●	▲										12.7	4.76	1.2	2.2	5.16	
	NP-CNGA120404TA4	●	●	▲	●		●	●						12.7	4.76	0.4	1.8	5.16	
	NP-CNGA120408TA4	●	●	▲	●		●	●						12.7	4.76	0.8	2.0	5.16	
NP-CNGA120412TA4	●	●	▲	●		●	●						12.7	4.76	1.2	2.2	5.16		
NP-CNGA120404TH4	●	●	▲	●		●							12.7	4.76	0.4	1.8	5.16		
NP-CNGA120408TH4	●	●	▲	●		●							12.7	4.76	0.8	2.0	5.16		
NP-CNGA120412TH4	●	●	▲	●		●							12.7	4.76	1.2	2.2	5.16		
ニューブチカット * (ワイパー)	NP-CNGA120404FSWS4	●	●	▲	▲		●							12.7	4.76	0.4	1.8	5.16	
	NP-CNGA120408FSWS4	●	●	▲	▲		●							12.7	4.76	0.8	2.0	5.16	
	NP-CNGA120412FSWS4	●	●	▲	▲		●							12.7	4.76	1.2	2.2	5.16	
	NP-CNGA120404GSWS4	●	●	▲										12.7	4.76	0.4	1.8	5.16	
	NP-CNGA120408GSWS4	●	●	▲										12.7	4.76	0.8	2.0	5.16	
	NP-CNGA120412GSWS4	●	●	▲										12.7	4.76	1.2	2.2	5.16	
	NP-CNGA120404GAWS4	●	●	▲	●		●							12.7	4.76	0.4	1.8	5.16	
	NP-CNGA120408GAWS4	●	●	▲	●		●							12.7	4.76	0.8	2.0	5.16	
NP-CNGA120412GAWS4	●	●	▲	●		●							12.7	4.76	1.2	2.2	5.16		

* ワイパーインサートは、B012ページを参照の上、ご使用ください。

● = NEW

● : 標準在庫品
▲ : 現在標準在庫品で将来新製品と置き換わる製品
(1ケース1個入りです)

▲ 2023年3月受注終了予定材種 : MB710, MB730
代替材種はB008をご参照ください。