





# BRP

刃先 R (APMX)	シャンク	呼び記号	在庫	刃数	寸法 (mm)							*  		 	
					R	DCX	DC	LF	DCON	LH	AZ	B2	APMX	クランプねじ	レンチ
6	R	BRP6PR322S32	▲	2	32	19.8	125	32	45	4	1°37'	6	TS43	TKY15D	①RPMW1204M0 ②RPMT1204M0E-JS
		BRP6PR403S32	▲	3	40	27.9	125	32	45	4	—	6	TS43	TKY15D	
		BRP6PR504S32	▲	4	50	37.8	150	32	50	4	—	6	TS43	TKY15D	
		BRP6PR504S42	▲	4	50	37.8	150	42	50	4	—	6	TS43	TKY15D	
	L	BRP6PR322LS32	▲	2	32	19.8	200	32	120	4	0°33'	6	TS43	TKY15D	
		BRP6PR403LS32	▲	3	40	27.9	200	32	120	4	—	6	TS43	TKY15D	
		BRP6PR504LS32	▲	4	50	37.8	250	32	150	4	—	6	TS43	TKY15D	
		BRP6PR504LS42	▲	4	50	37.8	250	42	150	4	—	6	TS43	TKY15D	
	EL	BRP6PR322ELS32	▲	2	32	19.8	300	32	50	4	1°26'	6	TS43	TKY15D	
		BRP6PR403ELS32	▲	3	40	27.9	300	32	50	4	—	6	TS43	TKY15D	
		BRP6PR403ELS42	▲	3	40	27.9	300	42	50	4	2°44'	6	TS43	TKY15D	
		BRP6PR504ELS42	▲	4	50	37.8	300	42	50	4	—	6	TS43	TKY15D	
8	R	BRP8PR402S32	▲	2	40	23.8	125	32	45	5.5	—	8	TS54	TKY25D	①RPMW1606M0 ②RPMT1606M0E-JS
		BRP8PR503S32	▲	3	50	33.8	150	32	50	5.5	—	8	TS54	TKY25D	
		BRP8PR503S42	▲	3	50	33.8	150	42	50	5.5	—	8	TS54	TKY25D	
		BRP8PR634S32	▲	4	63	46.8	150	32	50	5.5	—	8	TS54	TKY25D	
		BRP8PR634S42	▲	4	63	46.8	150	42	50	5.5	—	8	TS54	TKY25D	
	L	BRP8PR402LS32	▲	2	40	23.8	200	32	120	5.5	—	8	TS54	TKY25D	
		BRP8PR503LS32	▲	3	50	33.8	250	32	150	5.5	—	8	TS54	TKY25D	
		BRP8PR503LS42	▲	3	50	33.8	250	42	150	5.5	—	8	TS54	TKY25D	
		BRP8PR634LS32	▲	4	63	46.8	250	32	150	5.5	—	8	TS54	TKY25D	
		BRP8PR634LS42	▲	4	63	46.8	250	42	150	5.5	—	8	TS54	TKY25D	
	EL	BRP8PR402ELS32	▲	2	40	23.8	300	32	50	5.5	—	8	TS54	TKY25D	
		BRP8PR402ELS42	▲	2	40	23.8	300	42	50	5.5	2°52'	8	TS54	TKY25D	
BRP8PR503ELS42		▲	3	50	33.8	300	42	50	5.5	—	8	TS54	TKY25D		
BRP8PR634ELS42		▲	4	63	46.8	300	42	50	5.5	—	8	TS54	TKY25D		

注 Rはレギュラー、Lはロング、ELはエクストラロングタイプです。

\* 締付けトルク(N・m) : TS43=3.5, TS54=7.5