

VAPDM

呼び記号	DC	LCF	OAL	LF	PL	DCON	在庫	図番	呼び記号	DC	LCF	OAL	LF	PL	DCON	在庫	図番
VAPDM0960	9.60	87.0	142.0	140	2.0	10	●	1	VAPDM1450	14.5	108.0	168.0	165	3.0	16	●	1
VAPDM0970	9.70	87.0	142.0	140	2.0	10	●	1	VAPDM1500	15.0	108.1	168.1	165	3.1	16	●	1
VAPDM0980	9.80	87.0	142.0	140	2.0	10	●	1	VAPDM1550	15.5	113.2	173.2	170	3.2	16	●	1
VAPDM0990	9.90	87.1	142.1	140	2.1	10	●	1	VAPDM1600	16.0	113.3	173.3	170	3.3	16	●	1
VAPDM1000	10.0	87.1	142.1	140	2.1	10	●	1	VAPDM1650	16.5	113.4	173.4	170	3.4	20	●	1
VAPDM1010	10.1	87.1	147.1	145	2.1	12	●	1	VAPDM1700	17.0	113.5	178.5	175	3.5	20	●	1
VAPDM1020	10.2	87.1	147.1	145	2.1	12	●	1	VAPDM1750	17.5	118.6	183.6	180	3.6	20	●	1
VAPDM1030	10.3	87.1	147.1	145	2.1	12	●	1	VAPDM1800	18.0	118.7	183.7	180	3.7	20	●	1
VAPDM1040	10.4	87.2	147.2	145	2.2	12	●	1	VAPDM1850	18.5	123.8	188.8	185	3.8	20	●	1
VAPDM1050	10.5	87.2	147.2	145	2.2	12	●	1	VAPDM1900	19.0	123.9	188.9	185	3.9	20	●	1
VAPDM1060	10.6	87.2	147.2	145	2.2	12	●	1	VAPDM1950	19.5	124.0	189.0	185	4.0	20	●	1
VAPDM1070	10.7	94.2	154.2	152	2.2	12	●	1	VAPDM2000	20.0	124.1	189.1	185	4.1	20	●	1
VAPDM1080	10.8	94.2	154.2	152	2.2	12	●	1	VAPDM2050	20.5	129.3	204.3	200	4.3	25	●	1
VAPDM1090	10.9	94.3	154.3	152	2.3	12	●	1	VAPDM2100	21.0	129.4	204.4	200	4.4	25	●	1
VAPDM1100	11.0	94.3	154.3	152	2.3	12	●	1	VAPDM2110	21.1	129.4	204.4	200	4.4	25	●	1
VAPDM1110	11.1	94.3	154.3	152	2.3	12	●	1	VAPDM2120	21.2	129.4	204.4	200	4.4	25	●	1
VAPDM1120	11.2	94.3	154.3	152	2.3	12	●	1	VAPDM2150	21.5	129.5	204.5	200	4.5	25	●	1
VAPDM1130	11.3	94.3	154.3	152	2.3	12	●	1	VAPDM2200	22.0	129.6	204.6	200	4.6	25	●	1
VAPDM1140	11.4	94.4	154.4	152	2.4	12	●	1	VAPDM2250	22.5	134.7	209.7	205	4.7	25	●	1
VAPDM1150	11.5	94.4	154.4	152	2.4	12	●	1	VAPDM2300	23.0	134.8	209.8	205	4.8	25	●	1
VAPDM1160	11.6	94.4	154.4	152	2.4	12	●	1	VAPDM2350	23.5	134.9	209.9	205	4.9	25	●	1
VAPDM1170	11.7	94.4	154.4	152	2.4	12	●	1	VAPDM2400	24.0	140.0	215.0	210	5.0	25	●	1
VAPDM1180	11.8	94.4	154.4	152	2.4	12	●	1	VAPDM2450	24.5	140.1	215.1	210	5.1	25	●	1
VAPDM1190	11.9	101.5	161.5	159	2.5	12	●	1	VAPDM2500	25.0	140.2	215.2	210	5.2	25	●	1
VAPDM1200	12.0	101.5	161.5	159	2.5	12	●	1	VAPDM2550	25.5	145.3	225.3	220	5.3	32	●	1
VAPDM1210	12.1	101.5	161.5	159	2.5	12	●	1	VAPDM2600	26.0	145.4	225.4	220	5.4	32	●	1
VAPDM1220	12.2	101.5	161.5	159	2.5	12	●	1	VAPDM2650	26.5	145.5	225.5	220	5.5	32	●	1
VAPDM1230	12.3	101.6	161.6	159	2.6	12	●	1	VAPDM2700	27.0	145.6	225.6	220	5.6	32	●	1
VAPDM1240	12.4	101.6	161.6	159	2.6	12	●	1	VAPDM2800	28.0	145.8	225.8	220	5.8	32	●	1
VAPDM1250	12.5	101.6	161.6	159	2.6	12	●	1	VAPDM2900	29.0	151.0	231.0	225	6.0	32	●	1
VAPDM1260	12.6	101.6	161.6	159	2.6	12	●	1	VAPDM3000	30.0	151.2	231.2	225	6.2	32	●	1
VAPDM1270	12.7	101.6	161.6	159	2.6	12	●	1	VAPDM3100	31.0	156.4	236.4	230	6.4	32	●	1
VAPDM1280	12.8	101.7	161.7	159	2.7	12	●	1	VAPDM3200	32.0	161.6	241.6	235	6.6	32	●	1
VAPDM1290	12.9	101.7	161.7	159	2.7	12	●	1									
VAPDM1300	13.0	101.7	161.7	159	2.7	12	●	1									
VAPDM1350	13.5	102.8	162.8	160	2.8	16	●	1									
VAPDM1400	14.0	102.9	162.9	160	2.9	16	●	1									
VAPDM1410	14.1	107.9	167.9	165	2.9	16	●	1									
VAPDM1420	14.2	107.9	167.9	165	2.9	16	●	1									