

SANITARY PIPE FITTINGS

サニタリー管用継手

—両溶接タイプ—



◎ CADデータフォルダ名: 52_Sanitary_Vacuum_Tanks

■ 両溶接エルボ

Type	材質
SNWE	SUS304
SNWES	SUS316L

RoHS10

型式		D	d	L	SNWE		SNWES	
Type	No.				¥基準単価 1~9コ	¥スライド単価 10~20	¥基準単価 1~9コ	¥スライド単価 10~20
SNWES	8A	13.8	10.5	38	—	—	4,300	3,870
	10A	17.3	14.0		—	—	4,240	3,660
	15A	21.7	17.5		—	—	3,860	3,470
SNWE SNWES	1S	25.4	23	34	1,680	1,530	2,140	1,800
	1.5S	38.1	35.7	49	1,730	1,580	2,370	2,040
	2S	50.8	47.8	61	2,100	1,910	2,990	2,580
	2.5S	63.5	59.5	84	3,680	3,350	5,910	5,320
	3S	76.3	72.3	89	4,910	4,660	6,940	6,250

☞表示数量超えはWOSIにてご確認ください。

■ 両溶接45°エルボ

Type	材質
SNWHE	SUS304
SNWHES	SUS316L

RoHS10

型式		D	d	L	SNWHE		SNWHES	
Type	No.				¥基準単価 1~9コ	¥スライド単価 10~20	¥基準単価 1~9コ	¥スライド単価 10~20
SNWHE SNWHES	1S	25.4	23	15.8	2,130	1,670	2,500	1,830
	1.5S	38.1	35.7	23.7	2,490	2,000	2,950	2,280
	2S	50.8	47.8	31.6	3,120	2,440	3,750	2,950
	2.5S	63.5	59.5	42	5,400	4,440	7,060	5,540
	3S	76.3	72.3	52.6	6,750	5,440	8,510	7,240

☞表示数量超えはWOSIにてご確認ください。

■ 両溶接チーズ

Type	材質
SNWTT	SUS304
SNWTS	SUS316L

RoHS10

型式		D	d	L	SNWTT		SNWTS	
Type	No.				¥基準単価 1~9コ	¥スライド単価 10~20	¥基準単価 1~9コ	¥スライド単価 10~20
SNWTT SNWTS	1S	25.4	23.0	34.0	3,170	2,740	5,490	4,190
	1.5S	38.1	35.7	49.0	3,190	2,870	5,390	4,330
	2S	50.8	47.8	61.0	3,860	3,340	5,850	5,270
	2.5S	63.5	59.5	84.0	6,240	5,620	9,610	7,720
	3S	76.3	72.3	89.0	7,630	6,600	11,660	9,370

☞表示数量超えはWOSIにてご確認ください。

■ 両溶接異径チーズ

Type	材質
SNWTD	SUS304

RoHS10

型式		D1	d1	D2	d2	L1	L2	¥基準単価
Type	No.							1~10コ
SNWTD	1.5S-1S	38.1	35.7	25.4	23.0	49	45	4,610
	2S-1S	50.8	47.8	25.4	23.0	61	51	4,890
	2S-1.5S	50.8	47.8	38.1	35.7	61	64	5,800
	2.5S-1.5S	63.5	59.5	38.1	35.7	84	70	7,700
	2.5S-2S	63.5	59.5	50.8	47.8	84	82	7,900

☞表示数量超えはWOSIにてご確認ください。

■ ブラインドナット

Type	材質
SNYBN	SUS304

RoHS10

型式		A	B	(T)	¥基準単価	¥スライド単価
Type	No.				1~4コ	5~10
SNYBN	1S	46.0	53.1	30.0	5,000	4,900
	1.5S	56.0	64.6		5,300	4,900
	2S	71.0	81.9		5,500	5,400
	2.5S	85.0	98.1		7,800	7,700
	3S	100.0	115.4		9,500	9,300

☞表示数量超えはWOSIにてご確認ください。

Order 注文例: 型式 SNWE2S

Delivery 出荷日: 下記以外 在庫品 翌日出荷 ☑ P.133

☞ご希望によりPM6:00迄、当日出荷受付致します。

●SNWTS・SNWTD・SNYBN

3 日日出荷

