



URETHANES FOR HEAVY LOAD 高荷重用ウレタン



A



D	D T	d T	L T
15			
20			
25	±0.2	±0.2	±0.3
30			
40			
50	±0.3	±0.2	±0.5
60			
80	±0.4	±0.2	±0.5
100			

📄 製品概要 P.1633
📈 荷重グラフ P.1635
📦 硬度 ショアA90

F=L×15%		F=L×20%		F=L×25%			d	型式	
F mm	荷重 N(kgf)	F mm	荷重 N(kgf)	F mm	荷重 N(kgf)	V		Type	D - L
3.8	588 {60}	5.0	785 {80}	6.3	981 {100}	18	7	A 15	25
4.5		6.0		7.5					30
5.3		7.0		8.8					35
6.0		8.0		10.0					40
3.8	1128 {115}	5.0	1422 {145}	6.3	1765 {180}	24	8.5	A 20	25
4.5		6.0		7.5					30
5.3		7.0		8.8					35
6.0		8.0		10.0					40
3.8	1667 {170}	5.0	2157 {220}	6.3	2648 {270}	30	11	A 25	25
4.5		6.0		7.5					30
5.3		7.0		8.8					35
6.0		8.0		10.0					40
6.8		9.0		11.3					45
7.5		10.0		12.5					50
3.8	2599 {265}	5.0	3040 {310}	6.3	3531 {360}	37	14	A 30	25
4.5		6.0		7.5					30
5.3		7.0		8.8					35
6.0		8.0		10.0					40
6.8		9.0		11.3					45
7.5		10.0		12.5					50
8.3		11.0		13.8					55
9.0		12.0		15.0					60
6.0	4560 {465}	8.0	5394 {550}	10.0	6276 {640}	48	14	A 40	40
7.5		10.0		12.5					50
9.0		12.0		15.0					60
7.5	7747 {790}	10.0	9218 {940}	12.5	10787 {1100}	60	14	A 50	50
9.0		12.0		15.0					60
12.0		16.0		20.0					80
7.5	13042 {1330}	10.0	15102 {1540}	12.5	17652 {1800}	72	14	A 60	50
9.0		12.0		15.0					60
12.0		16.0		20.0					80
9.0	21378 {2180}	12.0	25399 {2590}	15.0	29420 {3000}	95	22	A 80	60
12.0		16.0		20.0					80
15.0		20.0		25.0					100
12.0	35990 {3670}	16.0	42659 {4350}	20.0	49720 {5070}	119	22	A100	80
15.0		20.0		25.0					100
18.0		24.0		30.0					120

•荷重 [kgf] = 荷重N×0.101972



Order
注文例

型式

A 25-40



Alterations
追加加工



型式 - (C1)

A 60-80 - C1




3 日目出荷



Delivery
出荷日



在庫品

追加加工	記号	詳細
	C1	内径にC1面取り加工