

ストロークエンドパイプ



Technical drawing of a circular metal bracket with two mounting holes. The drawing includes a side view and a top view.

Side View Dimensions:

- Overall diameter: D_1
- Mounting hole diameter: d
- Mounting hole spacing: 25
- Bracket thickness: 3
- Inner diameter of mounting hole: $\phi 13$
- Dimension L_1 (from center to mounting hole center)
- Dimension L (from center to mounting hole center, with tolerance $+0.3/0$)
- ESBT label

Top View Dimensions:

- Overall diameter: 20
- Mounting hole diameter: 20
- Mounting hole spacing: $W \pm 0.5$
- Labels A and B indicating material specifications

Legend:

- (A) 材質 SGP
- (B) 材質 SS400

ESBT		D ₁	d	d ₁	t	型式		L	Color 保安色
D	L ₁					Type	No.		
40	80	60.5	52.9	9	3.8	PHN	40	60	R (Red)
50	110	89.1	80.7		4.2		50	85	
70	110	101.6	93.2	13	4.2		70	85	
70	140	101.6	93.2	9	4.2		70	110	
70	140	101.6	93.2	13	4.2		7022	110	Y (Yellow)
90	140	139.8	130.8		4.5		90	110	
100	140	152.5	142.5		5		100	110	



L

L

Color

PH 70

—

R



在 庫 品