



〈SS 規格〉

寸法許容差の材質群は P9 同様 (単位 mm)

呼び番号	Oリングの寸法						
	太さ d2			内径 d1	材質群別許容差		
	①	②・③	①		②	③	
*SS-005			0.5				
*SS-008			0.8				
*SS-010			1				
*SS-012			1.2				
*SS-015			1.5				
*SS-018			1.8				
*SS-020			2				
*SS-022			2.2		±0.15	±0.20	
*SS-025			2.5				
*SS-028			2.8				
*SS-030			3				
*SS-032			3.2				
*SS-035			3.5				
*SS-038			3.8				
*SS-040			4				
*SS-042			4.2				
*SS-045			4.5				
*SS-048			4.8				
*SS-050			5				
*SS-055	1	±0.07	±0.10	5.5			
*SS-060			6				
*SS-065			6.5				
*SS-070			7				
*SS-075			7.5				
*SS-080			8	±0.10	±0.25	±0.30	
*SS-085			8.5				
*SS-090			9				
*SS-095			9.5				
*SS-100			10				
*SS-105			10.5				
*SS-110			11				
*SS-115			11.5				
*SS-120			12				
*SS-125			12.5				
*SS-130			13				
*SS-135			13.5				
*SS-140			14		±0.35	±0.40	
*SS-145			14.5				
*SS-150			15				
*SS-155			15.5				

呼び番号	Oリングの寸法						
	太さ d2			内径 d1	材質群別許容差		
	①	②・③	①		②	③	
*SS-160			16				
*SS-165			16.5		±0.35	±0.40	
*SS-170			17				
*SS-175			17.5				
*SS-180	1	±0.07	±0.10	18	±0.10		
*SS-185			18.5		±0.45	±0.50	
*SS-190			19				
*SS-195			19.5				
*SS-200			20				