



軸径 φ d	外径 φ D	厚 b	AC 型	AD 型	AE 型	UD 型	UE 型	KD 型	KE 型	特殊型式
10	14	2.5							KE	
10	14	3						KD		
10	16	3						KD		
10	16	4	AC							
10	18	4					UE			
10	18	5		AD						
10	18	6		AD						
10	20	4							※KE	
10	20	5		AD						
10	20	7	※AC	※AD		※UD	※UE			
10	21	8	AC							
10	22	7		※AD						
10	22	8		AD			UE			
10	24	6					UE			
10	24	7		AD						
10	25	4.5						KD		
10	25	5							KE	
10	25	7	※AC	※AD			※UE			KES-1 KCF
10	25	8	AC							
10	26	5		AD						
10	26	7		AD						
10	28	8	AC							
10	30	7		AD						
11	17	3								KDS-1
11	17	4	AC					KD		
11	20	4							KE	
11	22	4							※KE	
11	22	7		※AD						
11	25	7		※AD						
11	26	7		AD						
12	16	2.5							KE	
12	16	3						KD		
12	18	3						KD	KE	
12	18	5						KD		
12	19	3						KD		
12	20	5	AC							
12	20	6	AC	AD			UE			
12	22	4						※KD	※KE	
12	22	5							KE	
12	22	6		AD						
12	22	7	※AC	※AD			※UE			
12	23	5							KE	
12	24	7	※AC	※AD			※UE			
12	25	4								KES-1
12	25	5							KE	
12	25	7	※AC	※AD		※UD	※UE			UES-4 KCF
12	28	5		AD						
12	28	7	AC	AD		UD	UE			

※印は JIS 寸法 太字は在庫対象品となります

◎ 寸法表は変更する場合があります