




ソケット
SH(ホースニップル形)



品番	適用 ホース	寸				法 (mm)					重量 (g)
		L	φD	φd	S	C	sφ ₁	sφ ₂	φB	φT	
CKC02SH2	1/4"	55	21	18	17	18.5	29.5	18	5	8	59
CKC03SH2	3/8"	61	21	18	17	18.5	29.5	18	7	12	65

SM(オネジ形)



品番	接続形状 T	寸				法 (mm)					重量 (g)
		L	φD	φd	S	C	sφ ₁	sφ ₂	φB		
CKC02SM2	R1/4"	51	21	18	17	18.5	29.5	18	6	65	
CKC03SM2	R3/8"	53	21	18	17	18.5	29.5	18	6	75	

SF(メネジ形)


品番	接続形状 T	寸				法 (mm)					重量 (g)
		L	φD	φd	S	C	sφ ₁	sφ ₂	φB		
CKC02SF2	Rc1/4"	49	21	18	17	18.5	29.5	18	6	67	

プラグ
PH(ホースニップル形)


品番	適用 ホース	寸				法 (mm)					重量 (g)
		L	φH	φ ₁	φ ₂	φT	φB ₁	φB ₂			
CKC02PH2	1/4"	50	12	29	15	8.5	5	5	17		
CKC03PH2	3/8"	50	15.5	29	15	12	6	6	19		

PM(オネジ形)


品番	接続形状 T	寸			法 (mm)					重量 (g)
		L	S	C	φ	φB ₁	φB ₂			
CKC01PM2	R1/8"	31	12	13	15	6	6	12		
CKC02PM2	R1/4"	34	14	15.5	15	6	6	20		
CKC03PM2	R3/8"	35	19	21	15	9	6	33		

PML(オネジ形)


品番	接続形状 T	寸		法 (mm)					重量 (g)
		L	二面巾	φ	φB ₁	φB ₂			
CKC01PML2	R1/8"	33	14	15	6	6	26		
CKC02PML2	R1/4"	33	14	15	6	6	28		