



● 材質・仕上げ

 RoHS2適合

VGE	
本体	ガラス繊維強化ナイロン66
ベアリング	スチール

品番 	価格 (円)	アイドラー								ベアリング				質量 (kg)	適用アイドラー軸
		De	Da	Db	W	s2	θ (°)	r	h	呼び番号	d	D	B		標準アイドラー軸 Z → P.xxxx
VGE6002-6200	960	60	27	36	11.5	1.4	30	1.8	6.8	6200×1	10	30	9	0.05	Z6200-10・Z6200-12・Z6200-15

● 品番指定



VGE6002-6200


 軸穴・キー溝・押しねじ追加加工 → P.xxxx

対応不可