

■サイズ表

No.	A×B×C	D	E	F	G	H	I	J	リップ数	許容荷重kN	質量kg
CP07510	1000×750×125	18	23	16	50	-	-	-	2×3	8	221
CP09090	900×900×125	15	25	20	50	-	-	-	2×2	8	230
CP09012	1200×900×125	18	25	20	50	-	-	-	2×2	8	304
CP09018	1800×900×150	22	25	20	50	-	-	-	2×2	8	509
CP10010	1000×1000×125	18	25	20	50	-	-	-	2×2	8	285
CP10012	1200×1000×150	18	25	20	50	-	-	-	2×3	8	384
CP10015	1500×1000×150	18	25	20	50	-	-	-	2×3	8	454
CP10020	2000×1000×150	22	25	20	50	-	-	-	2×3	8	617
CP12012	1200×1200×150	22	20	15	-	-	-	-	3×3	12.5	405
CP12018	1800×1200×175	20	20	15	-	-	-	-	3×4	12.5	610
CP12024	2400×1200×200	35	30	18	-	-	-	-	3×7	16	1295
CP15030	3000×1500×250	42	35	20	-	-	-	-	3×6	25	2343
CP20020	2000×2000×320	40	35	25	100	20	100	9	3×3	25	2288
CP20030	3000×2000×270	45	40	25	-	20	100	8	4×6	25	3475

■仕様・価格表

* 標準在庫品

機械仕上				摺合B級				摺合A級			
オーダーNo.	No.	平面度: K	価格	オーダーNo.	No.	平面度: K	価格	オーダーNo.	No.	平面度: K	価格
* 940684	CP02020M	0.029	10,700	* 940721	CP02020B	0.019	25,200	* 940758	CP02020A	0.010	30,000
* 940685	CP02525M	0.033	14,100	* 940722	CP02525B	0.022	32,300	* 940759	CP02525A	0.011	37,600
* 940686	CP02530M	0.036	16,900	* 940723	CP02530B	0.023	33,300	* 940760	CP02530A	0.012	38,500
* 940687	CP03030M	0.038	21,200	* 940724	CP03030B	0.025	35,000	* 940761	CP03030A	0.012	46,400
* 940688	CP03035M	0.041	22,100	* 940725	CP03035B	0.026	37,700	* 940762	CP03035A	0.013	47,500
* 940689	CP03040M	0.043	26,600	* 940726	CP03040B	0.028	43,800	* 940763	CP03040A	0.014	54,000
* 940690	CP03045M	0.046	32,500	* 940727	CP03045B	0.030	59,000	* 940764	CP03045A	0.015	67,500
* 940691	CP03540M	0.045	32,500	* 940728	CP03540B	0.029	56,000	* 940765	CP03540A	0.015	67,000
* 940692	CP04545M	0.052	53,000	* 940729	CP04545B	0.033	98,000	* 940766	CP04545A	0.016	111,000
* 940693	CP04560M	0.060	83,500	* 940730	CP04560B	0.038	135,000	* 940767	CP04560A	0.019	155,000
* 940694	CP05050M	0.057	83,500	* 940731	CP05050B	0.036	117,000	* 940768	CP05050A	0.018	136,000
* 940695	CP05075M	0.070	142,000	* 940732	CP05075B	0.046	242,000	* 940769	CP05075A	0.022	289,000
* 940696	CP06060M	0.066	91,000	* 940733	CP06060B	0.042	169,000	* 940770	CP06060A	0.021	186,000
* 940697	CP06090M	0.082	161,000	* 940734	CP06090B	0.051	264,000	* 940771	CP06090A	0.026	309,000
* 940698	CP07510M	0.096	205,000	* 940735	CP07510B	0.060	353,000	* 940772	CP07510A	0.030	424,000
* 940699	CP09090M	0.095	231,000	* 940736	CP09090B	0.059	395,000	940773	CP09090A	0.029	436,000
* 940700	CP09012M	0.110	278,000	940737	CP09012B	0.068	675,000	940774	CP09012A	0.034	800,000
* 940701	CP09018M	0.144	487,000	940738	CP09018B	0.088	1,170,000	940775	CP09018A	0.044	1,310,000
* 940702	CP10010M	0.104	278,000	940739	CP10010B	0.065	495,000	940776	CP10010A	0.032	555,000
* 940703	CP10012M	0.115	402,000	940740	CP10012B	0.070	855,000	940777	CP10012A	0.035	980,000
* 940704	CP10015M	0.130	437,000	940741	CP10015B	0.080	885,000	940778	CP10015A	0.040	1,010,000
940705	CP10020M	0.159	665,000	940742	CP10020B	0.097	1,320,000	940779	CP10020A	0.049	1,470,000
940706	CP12012M	0.123	520,000	940743	CP12012B	0.076	940,000	940780	CP12012A	0.038	1,100,000
940707	CP12018M	0.154	805,000	940744	CP12018B	0.095	1,460,000	940781	CP12018A	0.047	1,680,000
940708	CP12024M	0.189	1,320,000	940745	CP12024B	0.115	2,330,000	940782	CP12024A	0.058	2,620,000
940709	CP15030M	0.233	2,210,000	940746	CP15030B	0.142	3,700,000	940783	CP15030A	0.071	4,360,000
940711	CP20020M	0.198	2,320,000	940748	CP20020B	0.121	都度見積	940785	CP20020A	0.061	都度見積
940712	CP20030M	0.250	3,800,000	940749	CP20030B	0.152	都度見積	940786	CP20030A	0.076	都度見積

■許容荷重について

下記条件による「はりの計算」に基づき算出、編集設定した値です。
定盤選定時の目安としてください。

- ・荷重条件：中央部に集中荷重
- ・支持条件：両端自由支持

■参照ページ

レバリングブロックA型



レバリングブロックA-U型

