

単品ブロックゲージ 0級相当品

BLOCK GAUGES (GRADE 0)



製品情報

高精度 0級相当モデル!



寸法精度規格

呼び寸法 (mm)		0級	
を超え	以下	寸法許容差 (μm)	寸法許容差幅 (μm)
—	10	± 0.12	0.10
10	25	± 0.14	0.10
25	50	± 0.20	0.10
50	75	± 0.25	0.12
75	100	± 0.30	0.12
125		± 0.40	0.14
150		± 0.40	0.14
175		± 0.50	0.16
200		± 0.50	0.16
250		± 0.60	0.16
300		± 0.70	0.18
400		± 0.90	0.20
500		± 1.10	0.25
600		± 1.30	0.25

用途 ● 一般測定、工作用の基準ゲージとして

● スペースブロックや高付加価値部品として使用

材質 ● 高炭素高クロム鋼

特長 ● 0級相当品

● 検査成績表付

仕様 ● 断面寸法: 10mm以下...30(0~-0.3)×9(-0.05~-0.2)mm
10mmを超え...35(0~-0.3)×9(-0.05~-0.2)mm

● 熱膨張係数: 11.5×10⁻⁶/K

※ JCSS校正サービスおよび別注製作非対応品です。

商品コード	品番	規格	標準小売価格	JAN (4975846)	商品コード	品番	規格	標準小売価格	JAN (4975846)	商品コード	品番	規格	標準小売価格	JAN (4975846)
150294	GB0-05	0.5mm	7,100	395961	150335	GB0-139	1.39mm	3,400	396364	150376	GB0-1450	14.50mm	5,800	396739
150295	GB0-10	1.0mm	3,400	395978	150336	GB0-140	1.40mm	3,400	396371	150377	GB0-1500	15.00mm	5,800	396746
150296	GB0-1-005	1.005mm	4,400	397132	150337	GB0-141	1.41mm	3,400	396388	150378	GB0-1550	15.50mm	5,800	396753
150297	GB0-101	1.01mm	3,400	395985	150338	GB0-142	1.42mm	3,400	396395	150379	GB0-1600	16.00mm	6,600	396760
150298	GB0-102	1.02mm	3,400	395992	150339	GB0-143	1.43mm	3,400	396401	150380	GB0-1650	16.50mm	6,600	396777
150299	GB0-103	1.03mm	3,400	396005	150340	GB0-144	1.44mm	3,400	396418	150381	GB0-1700	17.00mm	6,600	396784
150300	GB0-104	1.04mm	3,400	396012	150341	GB0-145	1.45mm	3,400	396425	150382	GB0-1750	17.50mm	6,600	396791
150301	GB0-105	1.05mm	3,400	396029	150342	GB0-146	1.46mm	3,400	396432	150383	GB0-1800	18.00mm	6,600	396807
150302	GB0-106	1.06mm	3,400	396036	150343	GB0-147	1.47mm	3,400	396449	150384	GB0-1850	18.50mm	6,600	396814
150303	GB0-107	1.07mm	3,400	396043	150344	GB0-148	1.48mm	3,400	396456	150385	GB0-1900	19.00mm	6,600	396821
150304	GB0-108	1.08mm	3,400	396050	150345	GB0-149	1.49mm	3,400	396463	150386	GB0-1950	19.50mm	6,600	396838
150305	GB0-109	1.09mm	3,400	396067	150346	GB0-150	1.50mm	3,400	396470	150387	GB0-2000	20.00mm	6,600	396845
150306	GB0-110	1.10mm	3,400	396074	150347	GB0-160	1.60mm	4,500	397149	150388	GB0-2050	20.50mm	6,600	396852
150307	GB0-111	1.11mm	3,400	396081	150348	GB0-170	1.70mm	4,500	397156	150389	GB0-2100	21.00mm	6,600	396869
150308	GB0-112	1.12mm	3,400	396098	150349	GB0-180	1.80mm	4,500	397163	150390	GB0-2150	21.50mm	6,600	396876
150309	GB0-113	1.13mm	3,400	396104	150350	GB0-190	1.90mm	4,500	397170	150391	GB0-2200	22.00mm	6,600	396883
150310	GB0-114	1.14mm	3,400	396111	150351	GB0-200	2.00mm	4,600	396487	150392	GB0-2250	22.50mm	6,600	396890
150311	GB0-115	1.15mm	3,400	396128	150352	GB0-250	2.50mm	4,600	396494	150393	GB0-2300	23.00mm	6,600	396906
150312	GB0-116	1.16mm	3,400	396135	150353	GB0-300	3.00mm	4,600	396500	150394	GB0-2350	23.50mm	6,600	396913
150313	GB0-117	1.17mm	3,400	396142	150354	GB0-350	3.50mm	4,600	396517	150395	GB0-2400	24.00mm	6,600	396920
150314	GB0-118	1.18mm	3,400	396159	150355	GB0-400	4.00mm	4,600	396524	150396	GB0-2450	24.50mm	6,600	396937
150315	GB0-119	1.19mm	3,400	396166	150356	GB0-450	4.50mm	4,600	396531	150397	GB0-2500	25.00mm	6,600	396944
150316	GB0-120	1.20mm	3,400	396173	150357	GB0-500	5.00mm	4,600	396548	150398	GB0-3000	30.00mm	7,500	396951
150317	GB0-121	1.21mm	3,400	396180	150358	GB0-550	5.50mm	4,600	396555	150399	GB0-4000	40.00mm	7,500	396968
150318	GB0-122	1.22mm	3,400	396197	150359	GB0-600	6.00mm	5,300	396562	150400	GB0-5000	50.00mm	8,300	396975
150319	GB0-123	1.23mm	3,400	396203	150360	GB0-650	6.50mm	5,300	396579	150401	GB0-6000	60.00mm	8,300	396982
150320	GB0-124	1.24mm	3,400	396210	150361	GB0-700	7.00mm	5,300	396586	150402	GB0-7000	70.00mm	8,500	396999
150321	GB0-125	1.25mm	3,400	396227	150362	GB0-750	7.50mm	5,300	396593	150403	GB0-7500	75.00mm	8,500	397002
150322	GB0-126	1.26mm	3,400	396234	150363	GB0-800	8.00mm	5,300	396609	150404	GB0-8000	80.00mm	8,500	397019
150323	GB0-127	1.27mm	3,400	396241	150364	GB0-850	8.50mm	5,300	396616	150405	GB0-9000	90.00mm	10,000	397026
150324	GB0-128	1.28mm	3,400	396258	150365	GB0-900	9.00mm	5,300	396623	150406	GB0-10000	100.00mm	11,500	397033
150325	GB0-129	1.29mm	3,400	396265	150366	GB0-950	9.50mm	5,300	396630	150407	GB0-12500	125mm	27,000	397040
150326	GB0-130	1.30mm	3,400	396272	150367	GB0-1000	10.00mm	5,300	396647	150408	GB0-15000	150mm	31,000	397057
150327	GB0-131	1.31mm	3,400	396289	150368	GB0-1050	10.50mm	5,300	396654	150409	GB0-17500	175mm	37,000	397064
150328	GB0-132	1.32mm	3,400	396296	150369	GB0-1100	11.00mm	5,800	396661	150410	GB0-20000	200mm	39,500	397071
150329	GB0-133	1.33mm	3,400	396302	150370	GB0-1150	11.50mm	5,800	396678	150411	GB0-25000	250mm	50,000	397088
150330	GB0-134	1.34mm	3,400	396319	150371	GB0-1200	12.00mm	5,800	396685	150412	GB0-30000	300mm	58,000	397095
150331	GB0-135	1.35mm	3,400	396326	150372	GB0-1250	12.50mm	5,800	396692	150413	GB0-40000	400mm	85,000	397101
150332	GB0-136	1.36mm	3,400	396333	150373	GB0-1300	13.00mm	5,800	396708	150414	GB0-50000	500mm	118,000	397118
150333	GB0-137	1.37mm	3,400	396340	150374	GB0-1350	13.50mm	5,800	396715	150415	GB0-60000	600mm	153,000	397125
150334	GB0-138	1.38mm	3,400	396357	150375	GB0-1400	14.00mm	5,800	396722					



ブロックゲージ

ピンゲージ

ピンバイス

ピンゲージ アクセサリ

リングゲージ

栓ゲージ

限界ゲージ

シフネスゲージ

テーパゲージ

溶接ゲージ

その他ゲージ