

並 目 ね じ 用

スプリュー種類明細表

ねじの呼び	自由外径		自由巻数 (±1/4)					呼称長さ (L ₂ mm)				
	最大	最小	1D	1.5D	2D	2.5D	3D	1D	1.5D	2D	2.5D	3D
No.2-56	3.02	2.79	3	5 1/8	7 3/8	9 1/2	11 3/4	2.18	3.28	4.37	5.46	6.55
No.4-40	4.04	3.66	2 3/4	4 3/4	6 3/4	8 7/8	10 7/8	2.84	4.27	5.69	7.11	8.53
No.5-40	4.39	4.01	3 1/4	5 1/2	7 3/4	10	12 1/4	3.18	4.76	6.35	7.94	9.53
No.6-32	4.90	4.52	2 3/4	4 3/4	6 7/8	8 7/8	10 7/8	3.50	5.26	7.01	8.76	10.52
No.8-32	5.59	5.21	3 1/2	6	8 3/8	10 3/4	13 1/4	4.17	6.26	8.33	10.42	12.49
No.10-24	6.58	6.20	2 7/8	5	7 1/8	9 1/4	11 3/4	4.33	7.24	9.65	12.07	14.49
No.12-24	7.24	6.86	3 1/2	6	8 3/8	10 5/8	13 1/8	5.49	8.23	10.97	13.72	16.46
1/4-20	8.38	7.87	3 3/8	5 3/4	8	10 3/8	12 3/4	6.35	9.52	12.70	15.87	19.05
5/16-18	10.16	9.65	4	6 5/8	9 1/4	—	—	7.94	11.91	15.88	—	—
3/8-16	11.99	11.48	4 3/8	7 1/4	10	—	—	9.52	14.29	19.05	—	—
7/16-14	14.00	13.36	4 1/2	7 3/8	10 1/4	—	—	11.11	16.67	22.22	—	—
1/2-13	15.80	15.16	4 7/8	7 7/8	11	—	—	12.70	19.05	25.40	—	—
9/16-12	17.63	16.99	5 1/8	8 1/4	11 1/2	—	—	14.29	21.43	28.58	—	—
5/8-11	19.48	18.85	5 1/4	8 1/2	11 3/4	—	—	15.88	23.83	31.75	—	—
3/4-10	23.01	22.38	5 7/8	9 3/8	13	—	—	19.05	28.58	38.10	—	—
7/8-9	26.72	25.96	6 1/4	10	13 3/4	—	—	22.22	33.34	44.45	—	—
1-8	30.38	29.62	6 3/8	10 1/8	14	—	—	25.40	38.10	50.80	—	—

細 目 ね じ 用

スプリュー種類明細表

ねじの呼び	自由外径		自由巻数 (±1/4)					呼称長さ (L ₂ mm)				
	最大	最小	1D	1.5D	2D	2.5D	3D	1D	1.5D	2D	2.5D	3D
No.6-40	4.90	4.39	3 1/2	6	8 3/8	—	—	3.50	5.26	7.01	8.76	10.52
No.8-36	5.69	5.18	3 7/8	6 1/2	9 1/8	11 5/8	—	4.17	6.25	8.33	10.42	12.50
No.10-32	6.50	5.99	4 1/8	6 7/8	9 1/2	12 1/4	14 7/8	4.83	7.24	9.65	12.07	14.48
1/4-28	8.28	7.77	5	8 1/4	11 3/8	14 1/2	17 5/8	6.35	9.52	12.70	15.88	19.05
5/16-24	10.16	9.65	5 1/2	8 7/8	12 1/4	15 5/8	19	7.94	11.91	15.88	19.84	23.83
3/8-24	11.89	11.38	6 7/8	11	15	19 1/8	—	9.52	14.29	19.05	23.83	28.58
7/16-20	13.94	13.31	6 5/8	10 5/8	14 5/8	—	—	11.11	16.67	22.22	27.79	—
1/2-20	15.67	15.04	7 7/8	12 3/8	16 7/8	—	—	12.70	19.05	25.40	31.75	—
9/16-18	17.55	16.92	8	12 1/2	17 1/8	—	—	14.29	21.43	28.58	35.71	—
5/8-18	19.25	18.62	9	14 1/8	19 1/4	—	—	15.88	23.81	31.75	39.67	—
3/4-16	22.88	22.25	9 3/4	15 1/8	20 5/8	—	—	19.05	28.58	38.10	—	—
7/8-14	26.70	25.93	9 7/8	15 1/2	21 1/8	—	—	22.22	33.34	44.45	—	—
1-12	30.45	29.69	9 5/8	14 7/8	20 1/8	—	—	25.40	38.10	50.80	—	—

サイズ表に記載されている製品は在庫しております。
他に、特殊サイズも製作致しますのでお問い合わせください。

