


●円すいころ軸受

メートル系



d 60~75 mm

主要寸法 mm							基本動 定格荷重	基本静 定格荷重	疲労限 荷重	許容回転速度		呼び番号 ²⁾
d	D	T	B	C	$r_s \text{ min}^{-1}$	$r_{ls} \text{ min}^{-1}$	C_r	C_{0r}	C_u	min ⁻¹		
										グリース	油潤滑	
60	85	17	17	14	1	1	56.5	83.0	10.1	4 000	5 300	○32912XA
	95	23	23	17.5	1.5	1.5	91.0	123	—	3 700	4 900	4T-32012X
	95	27	27	21	1.5	1.5	104	145	—	3 700	4 900	4T-33012
	100	30	30	23	1.5	1.5	126	164	—	3 600	4 700	4T-33112
	110	23.75	22	19	2	1.5	116	125	—	3 400	4 500	4T-30212
	110	29.75	28	24	2	1.5	144	164	20.1	3 400	4 500	32212U
	110	38	38	29	2	1.5	179	223	27.1	3 400	4 500	33212U
	115	40	39	33	2.5	2.5	209	249	—	3 200	4 300	4T-T2EE060
	125	37	33.5	26	3	3	161	186	—	2 800	3 700	4T-T7FC060
	130	33.5	31	26	3	2.5	199	210	25.6	3 000	4 000	30312U
	130	33.5	31	22	3	2.5	167	176	—	2 700	3 600	4T-30312D
	130	48.5	46	37	3	2.5	271	315	38.5	3 000	4 000	32312U
130	48.5	46	37	3	2.5	237	296	—	2 900	3 900	4T-32312C	
65	90	17	17	14	1	1	53.5	85.0	10.4	3 700	4 900	32913XU
	100	23	23	17.5	1.5	1.5	92.0	128	—	3 400	4 600	4T-32013X
	100	27	27	21	1.5	1.5	108	156	—	3 400	4 600	4T-33013
	110	34	34	26.5	1.5	1.5	160	211	—	3 300	4 400	4T-33113
	120	24.75	23	20	2	1.5	136	148	—	3 100	4 200	4T-30213
	120	32.75	31	27	2	1.5	176	206	25.1	3 100	4 200	32213U
	120	41	41	32	2	1.5	216	265	32.5	3 100	4 200	33213U
	140	36	33	28	3	2.5	225	238	28.7	2 800	3 700	30313U
	140	36	33	23	3	2.5	192	204	—	2 500	3 300	4T-30313D
140	51	48	39	3	2.5	305	350	42.5	2 800	3 700	32313U	
70	100	20	20	16	1	1	76.0	110	13.4	3 400	4 600	32914XU
	110	25	25	19	1.5	1.5	116	160	—	3 200	4 200	4T-32014X
	110	31	31	25.5	1.5	1.5	140	204	—	3 200	4 200	4T-33014
	120	37	37	29	2.5	0.6	190	251	30.5	3 100	4 100	33114U
	125	26.25	24	21	2	1.5	146	162	—	2 900	3 900	4T-30214
	125	33.25	31	27	2	1.5	184	220	26.8	2 900	3 900	32214U
	125	41	41	32	2	1.5	223	282	34.5	2 900	3 900	33214U
	140	39	35.5	27	3	3	191	231	—	2 400	3 200	4T-T7FC070
	150	38	35	30	3	2.5	255	272	32.0	2 600	3 500	30314U
	150	38	35	25	3	2.5	214	229	—	2 300	3 000	4T-30314D
	150	54	51	42	3	2.5	345	405	48.0	2 600	3 500	32314U
150	54	51	42	3	2.5	300	380	45.0	2 500	3 300	32314CU	
75	105	20	20	16	1	1	77.0	114	13.9	3 200	4 300	32915XU

注 1) 面取寸法 r または r_1 の最小許容寸法である。

2) ○印の付いた軸受はサブユニットの寸法を採用していない軸受である。