

屋内用
片扉 IP2XD
両扉 IP2XC

ライトベージュ塗装
LB色(5Y7.1)
日塗工J25-70B

クリーム塗装
クリーム色(2.5Y9.1)
日塗工J22-90B

フカサ 140mm

単位: mm

納期区分		木製基板付		納期区分		鉄製基板付		標準価格 円	扉形式	外形寸法			取付基板寸法		有効フカサ		製品質量 kg	
LB色	C色	品名	記号	LB色	C色	品名	記号			ヨコ	タテ	フカサ	ヨコ	タテ	Bタイプ	Sタイプ	Bタイプ	Sタイプ
◎◎	◎	B14-69		③	③	S14-69		42,000	片扉	600	900	140	520	820	108	121	27.4	31.3
◎◎	◎	B14-610		◎	③	S14-610		42,500	"	"	1,000	"	"	920	"	115	30.1	34.5
◎◎	◎	B14-74-2		◎	③	S14-74-2		35,500	両扉	700	400	140	620	320	108	121	17.3	19.2
◎◎	◎	B14-75-1		◎	③	S14-75-1		34,000	片扉	"	500	"	"	420	"	"	19.2	21.6
◎◎	◎	B14-76-1		③	③	S14-76-1		35,000	"	"	600	"	"	520	"	"	22.1	25.1
◎◎	◎	B14-77-1		③	③	S14-77-1		38,000	"	"	700	"	"	620	"	"	25.1	28.6
◎◎	◎	B14-78-1		③	③	S14-78-1		41,000	"	"	800	"	"	720	"	"	28.1	32.1
◎◎	◎	B14-79-2		③	③	S14-79-2		46,500	両扉	"	900	"	"	820	"	"	32.5	37.1
◎◎	◎	B14-710-2		③	③	S14-710-2		53,000	"	"	1,000	"	"	920	"	115	35.9	41.0
◎◎	◎	B14-84-2		③	③	S14-84-2		37,500	両扉	800	400	140	720	320	108	121	19.3	21.5
◎◎	◎	B14-85-2		③	③	S14-85-2		40,500	"	"	500	"	"	420	"	"	22.7	25.5
◎◎	◎	B14-86-2		③	③	S14-86-2		44,500	"	"	600	"	"	520	"	"	26.1	29.5
◎◎	◎	B14-87-2		③	③	S14-87-2		45,500	"	"	700	"	"	620	"	"	29.4	33.5
◎◎	◎	B14-88-2		③	③	S14-88-2		46,500	"	"	800	"	"	720	"	"	32.8	37.5
◎◎	◎	B14-89-2		◎	③	S14-89-2		52,000	"	"	900	"	"	820	"	"	36.2	41.5
◎◎	◎	B14-94-2		③	③	S14-94-2		40,500	両扉	900	400	140	820	320	108	121	21.2	23.7
◎◎	◎	B14-95-2		③	③	S14-95-2		44,500	"	"	500	"	"	420	"	"	25.0	28.1
◎◎	◎	B14-911-2		③	③	S14-911-2		66,500	"	"	1,100	"	"	1,020	"	115	47.8	55.2
◎◎	◎	B14-104-2		③	③	S14-104-2		42,500	両扉	1,000	400	140	920	320	108	115	23.2	25.9
◎◎	◎	B14-105-2		③	③	S14-105-2		46,500	"	"	500	"	"	420	"	"	27.3	30.8
③	③	B14-124-2		③	③	S14-124-2		48,500	両扉	1,200	400	140	1,120	320	108	115	27.1	30.4
◎◎	◎	B14-125-2		③	③	S14-125-2		50,500	"	"	500	"	"	420	"	"	31.9	36.2

フカサ 160mm

◎◎	◎	B16-33		◎◎	◎	S16-33		11,500	片扉	300	300	160	220	220	128	141	7.1	7.6
◎◎	◎	B16-34		◎◎	◎	S16-34		14,500	"	"	400	"	"	320	"	"	8.7	9.5
◎◎	◎	B16-345		◎◎	◎	S16-345		14,500	"	"	450	"	"	370	"	"	9.6	10.4
◎◎	◎	B16-35		◎◎	◎	S16-35		17,500	"	"	500	"	"	420	"	"	10.4	11.3
◎◎	◎	B16-36		◎◎	◎	S16-36		19,500	"	"	600	"	"	520	"	"	12.0	13.2
◎◎	◎	B16-3510		◎	③	S16-3510		37,000	片扉	350	1,000	160	270	920	128	135	20.7	23.1
③	③	B16-3511		③	③	S16-3511		39,000	"	"	1,100	"	"	1,020	"	"	22.5	25.1
③	③	B16-3512		③	③	S16-3512		41,000	"	"	1,200	"	"	1,120	"	"	24.3	27.2
③	③	B16-3513		③	③	S16-3513		42,500	"	"	1,300	"	"	1,220	"	"	26.1	29.3
③	③	B16-3514		③	③	S16-3514		46,500	"	"	1,400	"	"	1,320	"	"	30.6	33.9
◎	③	B16-3516		③	③	S16-3516		50,500	"	"	1,600	"	"	1,520	"	"	34.5	38.3
◎◎	◎	B16-43		◎◎	◎	S16-43		14,500	片扉	400	300	160	320	220	128	141	8.8	9.5
◎◎	◎	B16-44		◎◎	◎	S16-44		18,500	"	"	400	"	"	320	"	"	10.7	11.8
◎◎	◎	B16-45		◎◎	◎	S16-45		21,500	"	"	500	"	"	420	"	"	12.7	14.0
◎◎	◎	B16-46		◎◎	◎	S16-46		26,000	"	"	600	"	"	520	"	"	14.7	16.3
◎◎	◎	B16-47		◎◎	◎	S16-47		30,000	"	"	700	"	"	620	"	"	16.7	18.6
◎◎	◎	B16-48		◎◎	◎	S16-48		35,000	"	"	800	"	"	720	"	"	18.7	20.9
◎◎	◎	B16-410		◎◎	◎	S16-410		41,000	"	"	1,000	"	"	920	"	135	22.8	25.5
◎◎	◎	B16-412		③	③	S16-412		44,500	"	"	1,200	"	"	1,120	"	"	26.7	30.1
◎◎	◎	B16-53		◎◎	◎	S16-53		19,500	片扉	500	300	160	420	220	128	141	10.4	11.3
◎◎	◎	B16-54		◎◎	◎	S16-54		21,500	"	"	400	"	"	320	"	"	12.8	14.1
◎◎	◎	B16-55		◎◎	◎	S16-55		26,000	"	"	500	"	"	420	"	"	15.1	16.8
◎◎	◎	B16-56		◎◎	◎	S16-56		28,000	"	"	600	"	"	520	"	"	17.4	19.5
◎◎	◎	B16-57		◎◎	◎	S16-57		32,000	"	"	700	"	"	620	"	"	19.7	22.2
◎◎	◎	B16-58		◎◎	◎	S16-58		37,000	"	"	800	"	"	720	"	"	22.1	24.9
◎◎	◎	B16-59		◎◎	◎	S16-59		41,000	"	"	900	"	"	820	"	"	24.4	27.6

◎◎代理店様在庫品 ◎◎物流センター在庫品 ①③⑤⑦標準品(納期別) ◎受注品

上記品名記号はライトベージュ塗装です。
クリーム塗装にてご注文の際は品名記号の末尾にCを付けてご用命ください。
価格は同価格です。[例]B14-69→B14-69Cとなります。

◆有効フカサはハンドル部・フレーム枠などにより減少しますのでご注意ください。

★両扉の合わせ部の有効フカサは23mm引いた寸法となります。

■上記一部商品は、納期区分の変更(◎→③)をさせていただきますのでご了承ください。