

Parts No.	W	L	W ₁	W ₂	ℓ ₁	ℓ ₂	Holes	Chamfer Type
CWX-2875	28	75			45	15		C
CWX-28100		100			50			
CWX-28125		125			75	25		
CWX-28150		150			100			
CWX-3875	38	75			45	15		
CWX-38100		100			50			
CWX-38125		125			75	25	2	
CWX-38150		150			100			
CWX-4875	48				45	15		B
CWX-48100					50			
CWX-48125		125			75	25		
CWX-48150		150						
CWX-48200		200		—	100	50		
CWX-48250		250				25	3	
CWX-5875	58	75			45	15		
CWX-58100		100			50			
CWX-58150		150			100			
CWX-7575			75			25		
CWX-75100		100			50	25		
CWX-75125		125			75			
CWX-75150	75	150			100			
CWX-75200		200			150			
CWX-75250		250						
CWX-75300		300			100	50	3	
CWX-100100	100	100			50			A
CWX-100125		125			75			
CWX-100150		150	50	25	100	25		
CWX-100200		200			150			
CWX-100250		250			200			
CWX-100300		300				50		
CWX-125125	125	125	75		75		4	
CWX-125150		150			100			
CWX-125200		200	50	37.5	150	25		
CWX-125250		250						
CWX-125300		300			200	50		
CWX-150150		150	150			100		
CWX-150200	200		100	25	150	25		
CWX-150250	250				200			

CAD

LHS

Custom Bolt for CWX・CWXT CWX・CWXT固定専用低頭ボルト

- Parts No. : LHS-M1020
- CWX・CWXT固定専用低頭ボルトLHS-M1020は、CWX・CWXTプレートに付属しています。
- JIS規格のM10六角穴付ボルトに近似の破断トルクを有します。

N・m {kgf・m}

Parts No.	LHS-M1020
推奨締付トルク	67.2 {6.86}
破断トルク	118 {12.0}

※ボルトのみの販売もいたします。

