


ヘルールホースアダプタ/ヘルール異径ホースアダプタ/ヘルールキャップ (Rcネジ付)
Hose Adapter end Ferrule/Reducing Hose Adapter ends Ferrule/Ferrule cap

ヘルールホースアダプタ

Hose Adapter end Ferrule

Type HSAD-C





*SUS316Lのみ
Only SUS316L

Nom.size	OD1	OD2	ID1	ID2	A	L	Mass kg
1.0 ^S	25.4	23.7	23	21.4	50.5	85	0.14
1.25 ^S	31.8	30.1	29.4	27.8	50.5	90	0.15
1.5 ^S	38.1	36.4	35.7	34.1	50.5	100	0.18
2.0 ^S	50.8	49.1	47.8	44.8	64	125	0.36
2.5 ^S	63.5	61.8	59.5	57.5	77.5	140	0.56
3.0 ^S	76.3	74.6	72.3	70.3	91	160	0.78
3.5 ^S	89.1	87.4	85.1	82.1	106	160	1.07
4.0 ^S	101.6	99.9	97.6	94.6	119	170	1.28
*8A	13.8	12.8	10.5	10.5	34	42	0.050
*10A	17.3	16.3	14	14	34	42	0.050
*15A	21.7	20.7	17.5	17.5	34	42	0.060

ヘルール異径ホースアダプタ

Reducing Hose Adapter ends Ferrule

Type HSAD-CX




*すべて SUS316L
All SUS316L

Nom.size	OD1	OD2	ID1	ID2	A	Mass kg
1.0 ^S ×8A	13.8	12.8	10.5	23	50.5	0.098
1.0 ^S ×10A	17.3	16.3	14	23	50.5	0.099
1.0 ^S ×15A	21.7	20.7	17.5	23	50.5	0.107
1.5 ^S ×8A	13.8	12.8	10.5	35.7	50.5	0.083
1.5 ^S ×10A	17.3	16.3	14	35.7	50.5	0.086
1.5 ^S ×15A	21.7	20.7	17.5	35.7	50.5	0.096

ヘルールキャップ (Rcネジ付)

Ferrule cap (RC Screw)

Type CLF-BRC



*すべて SUS316L
All SUS316L

Nom.size	A	D	Mass kg
15A × Rc 1/4	34	21.7	0.042
15A × Rc 3/8	34	21.7	0.035
1.5 ^S × Rc 1/4	50.5	38.1	0.119
1.5 ^S × Rc 3/8	50.5	38.1	0.112
1.5 ^S × Rc 1/2	50.5	38.1	0.101
1.5 ^S × Rc 3/4	50.5	38.1	0.082
1.5 ^S × Rc 1	50.5	38.1	0.054
2.0 ^S × Rc 1/4	64	50.8	0.189
2.0 ^S × Rc 3/8	64	50.8	0.182
2.0 ^S × Rc 1/2	64	50.8	0.171
2.0 ^S × Rc 3/4	64	50.8	0.152