

前ページより

FROM

超硬シャンク ショートタイプ Carbide Shank, Short Type

(単位:mm) (Unit:mm)

ツールNo. EDP No.		呼び Designation	外径 DC	ボール 半径 RE	全長 LF	有効長		刃数 ZEFP	シャンク径 DCON	シャンク長 LS	首径 DN	標準価格 (Yen)
						首下長 LH	L/D					
①	7801429	PFB-R060SS06-S80CS	6	3	80	15	2.5	2	6	65	5.4	34,200
②	7801430	PFB-R080SS08-S100CS	8	4	100	20	2.5	2	8	80	7	35,800
③	7801431	PFB-R100SS10-S100CS	10	5	100	25	2.5	2	10	75	9	36,400
④	7801432	PFB-R120SS12-S110CS	12	6	110	30	2.5	2	12	80	11	42,700
⑤	7801433	PFB-R160SS16-S140CS	16	8	140	40	2.5	2	16	100	14	50,900
⑥	7801434	PFB-R200SS20-S160CS	20	10	160	50	2.5	2	20	110	18	72,500
⑦	7801435	PFB-R250SS25-S160CS	25	12.5	160	62.5	2.5	2	25	97.5	22	94,200
⑧	7801436	PFB-R300SS32-S170CS	30	15	170	75	2.5	2	32	95	27	119,000
⑨	7801437	PFB-R320SS32-S180CS	32	16	180	80	2.5	2	32	100	29	126,000

適用インサートと部品はp.905～907をご覧ください。
See p.905-907 for available inserts and parts.

超硬シャンク ロングタイプ Carbide Shank, Long Type

(単位:mm) (Unit:mm)

ツールNo. EDP No.		呼び Designation	外径 DC	ボール 半径 RE	全長 LF	有効長		刃数 ZEFP	シャンク径 DCON	シャンク長 LS	首径 DN	標準価格 (Yen)
						首下長 LH	L/D					
①	7801439	PFB-R060SS06-L100CS	6	3	100	30	5	2	6	70	5.4	37,200
②	7801440	PFB-R080SS08-L120CS	8	4	120	40	5	2	8	80	7	38,800
③	7801441	PFB-R100SS10-L130CS	10	5	130	50	5	2	10	80	9	39,300
④	7801442	PFB-R120SS12-L140CS	12	6	140	60	5	2	12	80	11	46,000
⑤	7801443	PFB-R160SS16-L160CS	16	8	160	72	4.5	2	16	88	14	54,600
⑥	7801444	PFB-R200SS20-L180CS	20	10	180	90	4.5	2	20	90	18	80,700
⑦	7801445	PFB-R250SS25-L200CS	25	12.5	200	100	4	2	25	100	22	106,000
⑧	7801446	PFB-R300SS32-L220CS	30	15	220	120	4	2	32	100	27	142,000
⑨	7801447	PFB-R320SS32-L230CS	32	16	230	128	4	2	32	102	29	150,000

適用インサートと部品はp.905～907をご覧ください。
See p.905-907 for available inserts and parts.

超硬シャンク エキストラロングタイプ Carbide Shank, Extra Long Type

(単位:mm) (Unit:mm)

ツールNo. EDP No.		呼び Designation	外径 DC	ボール 半径 RE	全長 LF	有効長		刃数 ZEFP	シャンク径 DCON	シャンク長 LS	首径 DN	標準価格 (Yen)
						首下長 LH	L/D					
①	7801419	PFB-R060SS06-LL120CS	6	3	120	42	7	2	6	78	5.4	39,100
②	7801420	PFB-R080SS08-LL140CS	8	4	140	56	7	2	8	84	7	40,900
③	7801421	PFB-R100SS10-LL150CS	10	5	150	70	7	2	10	80	9	41,500
④	7801422	PFB-R120SS12-LL160CS	12	6	160	84	7	2	12	76	11	52,200
⑤	7801423	PFB-R160SS16-LL200CS	16	8	200	96	6	2	16	104	14	57,500
⑥	7801424	PFB-R200SS20-LL240CS	20	10	240	120	6	2	20	120	18	86,700
⑦	7801425	PFB-R250SS25-LL260CS	25	12.5	260	137.5	5.5	2	25	122.5	22	124,000
⑧	7801426	PFB-R300SS32-LL290CS	30	15	290	165	5.5	2	32	125	27	177,000
⑨	7801427	PFB-R320SS32-LL300CS	32	16	300	176	5.5	2	32	124	29	187,000

適用インサートと部品はp.905～907をご覧ください。
See p.905-907 for available inserts and parts.