

一般用ねじ切り丸ダイス

Round Dies • Adjustable type for general use

RD(SKS)

メートルねじ(M)
Metric

(単位:mm) (Unit:mm)

ツール No. EDP No.	外径 D	ねじ	在庫 Stock	標準価格 (Yen)	ツール No. EDP No.	外径 D	ねじ	在庫 Stock	標準価格 (Yen)
46011	20	M2 × 0.4	A	5,210	46092	25	M9 × 0.5	D	11,300
46013		M2.2 × 0.45		5,390	46093		M10 × 1.5	B	4,820
46014		M2.2 × 0.25		8,510	46094		M10 × 1.25		4,820
46015		M2.3 × 0.4	D	5,390	46095		M10 × 1		6,340
46017		M2.5 × 0.45		5,390	46096		M10 × 0.75	D	8,340
46018		M2.5 × 0.35		8,510	46097		M10 × 0.5		11,300
46020		M2.6 × 0.45	A	5,210	46121		M5 × 0.9		8,610
46021		M2.6 × 0.35	D	8,510	46122		M5 × 0.8	B	8,610
46022		M3 × 0.6		4,060	46127		M6 × 1	A	7,200
46023		M3 × 0.5	A	4,060	46128		M6 × 0.75	D	13,200
46024		M3 × 0.35		6,560	46133		M8 × 1.25	A	7,200
46025		M3.5 × 0.6	D	5,390	46134		M8 × 1	B	9,310
46027		M3.5 × 0.35		6,560	46135		M8 × 0.75	D	13,200
46028		M4 × 0.75		4,060	46137		M9 × 1.25	B	8,610
46029		M4 × 0.7	A	4,060	46139		M9 × 1		10,700
46030		M4 × 0.5		6,560	46140		M9 × 0.75	D	15,800
46031		M4.5 × 0.75	D	5,820	46141		M9 × 0.5		15,800
46033		M5 × 0.9		4,060	46142		M10 × 1.5	A	7,200
46034		M5 × 0.8	A	4,060	46143		M10 × 1.25		7,200
46035		M5 × 0.5	D	6,560	46144		M10 × 1	B	9,310
46037	M5.5 × 0.5		5,820	46145	M10 × 0.75		15,800		
46038	M6 × 1	A	4,060	46146	M10 × 0.5		18,100		
46039	M6 × 0.75		6,560	46147	M11 × 1.5		9,750		
46040	M6 × 0.5	D	6,560	46148	M11 × 1.25	D	12,400		
46061	M3 × 0.6		4,820	46149	M11 × 1		12,400		
46062	M3 × 0.5	A	4,820	46150	M11 × 0.75		14,900		
46063	M3 × 0.35	D	7,530	46151	M11 × 0.5		16,100		
46064	M3.5 × 0.6	B	5,820	46152	M12 × 1.75		7,200		
46066	M3.5 × 0.35	D	7,530	46153	M12 × 1.5	A	7,200		
46067	M4 × 0.75		4,820	46154	M12 × 1.25		7,200		
46068	M4 × 0.7	A	4,820	46155	M12 × 1	B	9,310		
46069	M4 × 0.5	D	7,530	46156	M12 × 0.75		14,000		
46070	M4.5 × 0.75	B	5,820	46157	M12 × 0.5		16,100		
46072	M4.5 × 0.5	D	7,530	46158	M13 × 1.75		12,400		
46073	M5 × 0.9		4,820	46159	M13 × 1.5	D	12,400		
46074	M5 × 0.8	A	4,820	46160	M13 × 1		12,400		
46075	M5 × 0.75		7,530	46161	M13 × 0.75		16,100		
46076	M5 × 0.5	D	7,730	46162	M13 × 0.5		18,100		
46077	M5.5 × 0.9		7,530	46163	M14 × 2	A	7,200		
46078	M5.5 × 0.5		8,340	46164	M14 × 1.5		7,200		
46079	M6 × 1	A	4,820	46165	M14 × 1.25	B	11,400		
46080	M6 × 0.75	B	6,750	46166	M14 × 1		9,310		
46081	M6 × 0.5	D	7,730	46167	M14 × 0.75		18,100		
46082	M7 × 1	B	5,820	46168	M14 × 0.5		18,100		
46083	M7 × 0.75		7,730	46169	M15 × 2		10,500		
46084	M7 × 0.5	D	9,270	46170	M15 × 1.5	D	10,500		
46085	M8 × 1.25	A	4,820	46171	M15 × 1		12,400		
46086	M8 × 1	B	5,760	46172	M15 × 0.75		16,100		
46087	M8 × 0.75		6,270	46173	M15 × 0.5		16,100		
46088	M8 × 0.5	D	10,000	46174	M16 × 2	A	7,200		
46089	M9 × 1.25	B	6,070	46175	M16 × 1.5		7,200		
46090	M9 × 1	D	7,070	46176	M16 × 1.25	D	14,900		
46091	M9 × 0.75		8,340	46177	M16 × 1	B	8,610		

次ページへ

外径 D 38 ~ 63 NEXT

A, B, C, D=標準在庫品 A, B, C, D=Standard stock item. □=特定代理店在庫品 □=Stocked by specific distributors. Contact us for price & availability.