

内径プラグゲージ(LG)

Limit plug gauge for minor diameter



2級 (従来JIS)
Class 2 (Previous JIS)

メートル(M) ねじ Metric screw threads

呼び Thread Size	検査用 Inspection IM		工作用 Working WM	
	精度 Class	ツールNo. EDP No. 標準価格 (Yen)	精度 Class	ツールNo. EDP No. 標準価格 (Yen)
M 1.4 × 0.3	2	9329020 ¥25,000	2	9329021 ¥25,000
M 1.6 × 0.35	2	9329035 ¥25,000	2	9329036 ¥25,000
M 1.7 × 0.35	2	9329045 ¥25,000	2	9329046 ¥25,000
M 2 × 0.4	2	9329075 ¥23,200	2	9329076 ¥23,200
M 2.3 × 0.4	2	9329100 ¥23,200	2	9329101 ¥23,200
M 2.5 × 0.45	2	9329115 ¥20,400	2	9329116 ¥20,400
M 2.6 × 0.45	2	9329125 ¥20,400	2	9329126 ¥20,400
M 3 × 0.5	2	9329145 ¥20,400	2	9329146 ¥20,400
M 4 × 0.7	2	9329175 ¥11,820	2	9329176 ¥11,820
M 5 × 0.8	2	9329200 ¥11,000	2	9329201 ¥11,000
M 6 × 1	2	9329230 ¥11,000	2	9329231 ¥11,000
M 8 × 1.25	2	9329260 ¥10,380	2	9329261 ¥10,380
M 8 × 1	2	9329265 ¥10,380	2	9329266 ¥10,380
M 10 × 1.5	2	9329300 ¥11,000	2	9329301 ¥11,000
M 10 × 1.25	2	9329305 ¥11,000	2	9329306 ¥11,000
M 10 × 1	2	9329310 ¥11,000	2	9329311 ¥11,000

呼び Thread Size	検査用 Inspection IM		工作用 Working WM	
	精度 Class	ツールNo. EDP No. 標準価格 (Yen)	精度 Class	ツールNo. EDP No. 標準価格 (Yen)
M 12 × 1.75	2	9329350 ¥12,000	2	9329351 ¥12,000
M 12 × 1.5	2	9329355 ¥12,000	2	9329356 ¥12,000
M 12 × 1.25	2	9329360 ¥12,000	2	9329361 ¥12,000
M 12 × 1	2	9329365 ¥12,000	2	9329366 ¥12,000
M 14 × 2	2	9329410 ¥12,000	2	9329411 ¥12,000
M 14 × 1.5	2	9329415 ¥12,000	2	9329416 ¥12,000
M 16 × 2	2	9329470 ¥12,000	2	9329471 ¥12,000
M 16 × 1.5	2	9329475 ¥14,220	2	9329476 ¥14,220
M 18 × 2.5	2	9329530 ¥14,220	2	9329531 ¥14,220
M 18 × 1.5	2	9329540 ¥14,220	2	9329541 ¥14,220
M 20 × 2.5	2	9329600 ¥14,220	2	9329601 ¥14,220
M 20 × 1.5	2	9329605 ¥14,220	2	9329606 ¥14,220
M 22 × 2.5	2	9329645 ¥16,120	2	9329646 ¥16,120
M 22 × 1.5	2	9329655 ¥16,120	2	9329656 ¥16,120
M 24 × 3	2	9329690 ¥16,120	2	9329691 ¥16,120
M 24 × 1.5	2	9329705 ¥16,120	2	9329706 ¥16,120

在庫区分は全てD(標準在庫品)となります。
Stock are categorized in section D (Standard stock item).