











PB C6 992

ToolBox with 90 PrecisionBits: 10x C6 in 8 BitBlocks, 10x long type E6 L, with magnetic holder PB 451 M

ToolBox con 90 PrecisionBits: 10x C6 in 8 BitBlocks, 10x tipo lungo E6 L, con portainseriti magnetico PB 451 M

C6,3 (1/4")



										
PB C6.992	PB 451.M	2x2, 2x3, 2x4, 5	6x1, 7x2, 5x3, 1, 2	2x1, 2x2, 3, 1, 2	7, 8, 9, 3x10, 4x15, 6x20, 5x25, 27, 30, 3x30, 40, 2x40, 10, 15, 20, 25, 30, 40	8, 9, 10, 15, 20, 25, 30, 40	2.5, 2x3, 4x4, 4x5, 3x6	1029	1	7 610733 228126

PB E6 985

BitCase with belt-clip, with 10 PrecisionBits E6 in a BitBlock

BitCase con clip per cintura, 10 PrecisionBits E6 in BitBlock

E6,3 (1/4")



						
PB E6.985	1, 2, 3	15, 20, 25	3, 4, 5, 6	154	10	7 610733 207299