










外観				
型式	FL SWITCH 1005N FL SWITCH 1005NT	FL SWITCH 1008N FL SWITCH 1008NT	FL SWITCH 1105N FL SWITCH 1105NT	FL SWITCH 1108N FL SWITCH 1108NT
製品番号	1085039 1085170	1085256 1085165	1085254 1085163	1085243 1085162
RJ45ポート数	5	8	5	8
RJ45伝送速度	10/100Mbps	10/100Mbps	10/100/1000Mbps	10/100/1000Mbps
MACアドレス学習数	2K	2K	2K 4K	4K
ジャンボフレーム	—	—	○ (9kB)	○ (9kB)
EtherNet/IP優先制御 (QoS)	—	—	○	○

外観						
型式	FL SWITCH 1004N-FX FL SWITCH 1004N-FX ST FL SWITCH 1004N-FX SM	FL SWITCH 1004N-SFX FL SWITCH 1004NT-SFX	FL SWITCH 1005N-2SFX FL SWITCH 1005NT-2SFX	FL SWITCH 1104N-SFP	FL SWITCH 1105N-2SFP	FL SWITCH 1012NT-2SFP
製品番号	1084159 1085179 1085214	1085177 1085169	1085176 1085164	1085173	1085171	1249598
RJ45ポート数	4	4	5	4	5	12
RJ45伝送速度	10/100Mbps	10/100Mbps	10/100Mbps	10/100/1000Mbps	10/100/1000Mbps	10/100Mbps
光ポート数 (種別)	1	1 (SFP)	2 (SFP)	1 (SFP)	2 (SFP)	2 (SFP)
光伝送速度	100Mbps	100Mbps	100Mbps	100/1000Mbps	100/1000Mbps	100/1000Mbps
MACアドレス学習数	2K	2K	2K	4K	4K	8K
ジャンボフレーム	—	—	—	○ (9kB)	○ (9kB)	—
EtherNet/IP優先制御 (QoS)	—	—	—	○	○	—

SCマルチモード、STマルチモード、
SCシングルモードの3機種

外観				
型式	FL SWITCH 1016N	FL SWITCH 1116N	FL SWITCH 1608	FL SWITCH 1708
製品番号	1085255	1085219	1196227	1196228
RJ45ポート数	16	16	8 (M12 / D-code)	8 (M12 / X-code)
RJ45伝送速度	10/100Mbps	10/100/1000Mbps	10/100Mbps	10/100/1000Mbps
MACアドレス学習数	8K	8K	4K	4K
ジャンボフレーム	—	○ (9kB)	—	○ (9kB)
EtherNet/IP優先制御 (QoS)	—	○	○	○