


NSD ブランチティー

CAD
2D & 3D

RoHS対応



単位: mm

形 式	チューブ外径×内径 φ D	R	A	B	L1	L2	E1	(E2)	E3	C	対辺 H1	対辺 H2	質量 (g)	ナフィス径 (φmm)	CAD ファイル名
NSD0420-01□	4 × 2	R1/8	8	42	38	17	21	27.9	11.5	5.5	10	12	36	1.3	NSD0420-01
NSD0420-02□		R1/4	11	44		16	22	30.1				14	45		NSD0420-02
NSD0425-01□	4 × 2.5	R1/8	8	42	38	17	21	27.9	11.5	5.5	10	12	36	1.4	NSD0425-01
NSD0425-02□		R1/4	11	44		16	22	30.1				14	45		NSD0425-02
NSD0640-01□	6 × 4	R1/8	8	42	38	17	21	27.9	11.5	6	12	12	39	3	NSD0640-01
NSD0640-02□		R1/4	11	44		16	22	30.1				14	48		NSD0640-02
NSD0640-03□		R3/8	12	58	51.7	22.7	29	40				19	113		NSD0640-03
NSD0860-01□	8 × 6	R1/8	8	50	46	21	25	34.8	13.5	7	14	17	80	5	NSD0860-01
NSD0860-02□		R1/4	11		44	19		77				NSD0860-02			
NSD0860-03□		R3/8	12	58	51.7	22.7	29	40				19	112		NSD0860-03
NSD1075-02□	10 × 7.5	R1/4	11	58	52	23	29	40	16.5	9	17	19	121	6	NSD1075-02
NSD1075-03□		R3/8	12		51.7	22.7		23				120	NSD1075-03		
NSD1075-04□		R1/2	15	62	53.8	22.8	31	44.3				164	NSD1075-04		
NSD1080-02□	10 × 8	R1/4	11	58	52	23	29	40	16.5	9	17	19	120	6.5	NSD1080-02
NSD1080-03□		R3/8	12		51.7	22.7		119				NSD1080-03			
NSD1080-04□		R1/2	15	62	53.8	22.8	31	44.3				162	NSD1080-04		
NSD1290-02□	12 × 9	R1/4	11	58	52	23	29	40	16.5	9	19	19	126	7.5	NSD1290-02
NSD1290-03□		R3/8	12		51.7	22.7		127				NSD1290-03			
NSD1290-04□		R1/2	15	62	53.8	22.8	31	44.3				170	NSD1290-04		
NSD1210-02□	12 × 10	R1/4	11	58	52	23	29	40	16.5	9	19	19	124	8.5	NSD1210-02
NSD1210-03□		R3/8	12		51.7	22.7		125				NSD1210-03			
NSD1210-04□		R1/2	15	62	53.8	22.8	31	44.3				167	NSD1210-04		
NSD1613-03□	16 × 13	R3/8	12	64	57.7	25.7	32	45.3	18	9.5	23	23	172	11.5	NSD1613-03
NSD1613-04□		R1/2	15		55.8	23.8		174				NSD1613-04			

※. L寸法は、ねじ締付け後の参考寸法です。

※. 形式内の□につきましては、ネジ部にシールテープ仕様を希望する場合のみ記号: -TPをご記入ください。