

**KD**  
NO COVER


ブランチティー カバー無し

RoHS対応




OP.  
P.868

CAD  
2D & 3D



メートルネジの場合



管用テーパネジの場合

単位：mm

形式	チューブ外径 φD	R	A	B	L1	L2	φP	チューブ径 C	E	対辺 H	リフス径 (φmm)	質量 (g)	CAD ファイル名
KD4-M5-1□	4	M5×0.8	3	37.4	34.4	16.8	10.5	14.5	17.6	10	1.8	23	KD4-M5-1
KD4-01-1□		R1/8	8	40.4	36.4	18.8						26	KD4-01-1
KD4-02-1□		R1/4	11	43.4	37.4	19.8				35	KD4-02-1		
KD6-M5-1□	6	M5×0.8	3	42.2	39.2	19	12.5	16.6	20.2	12	1.8	33	KD6-M5-1
KD6-01-1□		R1/8	8	45.2	41.2	21						35	KD6-01-1
KD6-02-1□		R1/4	11	48.2	42.1	22				43	KD6-02-1		
KD6-03-1□		R3/8	12	50	43.6	23.5				56	KD6-03-1		
KD8-01-1□	8	R1/8	8	50.3	46.3	24	14.5	17.7	22.3	14	6	44	KD8-01-1
KD8-02-1□		R1/4	11	53.3	47.3	25						50	KD8-02-1
KD8-03-1□		R3/8	12	55.1	48.8	26.5				63	KD8-03-1		
KD10-01-1□	10	R1/8	8	58.6	54.6	28.5	18.5	20	26.1	17	6	80	KD10-01-1
KD10-02-1□		R1/4	11	61.6	55.6	29.5						83	KD10-02-1
KD10-03-1□		R3/8	12	62.6	56.3	30.2				91	KD10-03-1		
KD10-04-1□		R1/2	15	65.6	57.4	31.3				118	KD10-04-1		
KD12-02-1□	12	R1/4	11	67.2	61.2	31.5	21.5	22.6	29.7	21	8	132	KD12-02-1
KD12-03-1□		R3/8	12	68.2	61.9	32.2						138	KD12-03-1
KD12-04-1□		R1/2	15	71.2	63	33.3				154	KD12-04-1		

※1. テーパーネジタイプのL1、L2寸法は、ねじ締付け後の参考寸法です。

※2. 形式末尾の□には、シールゴム材質にFKMを希望される場合記号：-Fをご記入ください。