

リコイルパケット (METRIC)

並目	長さ	部品番号	入数
M2-0.4	1D	25022	10
	1.5D	25023	10
	2D	25024	10
M2.2-0.45	1.5D	25013	10
M2.5-0.45	1D	25252	10
	1.5D	25253	10
	2D	25254	10
M3-0.50	1D	25032	10
	1.5D	25033	10
	2D	25034	10
M3.5-0.60	1.5D	25353	10
M4-0.70	1D	25042	10
	1.5D	25043	10
	2D	25044	10
M5-0.80	1D	25052	10
	1.5D	25053	10
	2D	25054	10
M6-1.00	1D	25062	10
	1.5D	25063	10
	2D	25064	10
M7-1.00	1.5D	25073	10
M8-1.25	1D	25082	10
	1.5D	25083	10
	2D	25084	10
M9-1.25	1D	25092	10
	1.5D	25093	10
M10-1.50	1D	25102	10
	1.5D	25103	10
	2D	25104	10
M11-1.50	1.5D	25113	10
M12-1.75	1D	25122	10
	1.5D	25123	10
	2D	25124	10
M12-1.00	1.5D	28123-1	10
M13-1.75	1.5D	25133	5
M14-2.00	1D	25142	5
	1.5D	25143	5
	2D	25144	5
M15-2.00	1.5D	25153	5
M16-2.00	1D	25162	5
	1.5D	25163	5
	2D	25164	5
M18-2.50	1.5D	25153	5
M20-2.50	1.5D	25203	5
M22-2.50	1.5D	25223	3
M24-3.00	1.5D	25243	3

細目	長さ	部品番号	入数
M8-1.00	1D	27082	10
	1.5D	27083	10
	2D	27084	10
M9-1.00	1.5D	27093	10
M10-1.25	1D	27102	10
	1.5D	27103	10
	2D	27104	10
M11-1.25	1.5D	27113	10
M12-1.50	1D	27122	10
	1.5D	27123	10
	2D	27124	10
M13-1.50	1.5D	27133	5
M14-1.50	1D	27142	5
	1.5D	27143	5
	2D	27144	5
M16-1.50	1D	27162	5
	1.5D	27163	5
	2D	27164	5
M18-2.00	1.5D	27183	5
M20-2.00	1.5D	27203	5
M22-2.00	1.5D	27223	3
M24-2.00	1.5D	27243	3

極細目	長さ	部品番号	入数
M8-0.75	1.5D	28083	10
M10-1.00	1D	28102	10
	1.5D	28103	10
M11-1.00	1.5D	28113	10
M12-1.25	1D	28122	10
	1.5D	28123	10
	2D	28124	10
M13-1.25	1.5D	28133	5
M14-1.25	1.5D	28143-1.25	5
M18-1.50	1.5D	28183	5
M20-1.50	1.5D	28203	5
M22-1.50	1.5D	28223	3
M24-1.50	1.5D	28243	3

スパークプラグ	長さ	部品番号	入数
M10-1.00	6.8mm	28107	10
	0.339	28108	10
	1/2"	28109	10
	1D	28102	10
	1.5D	28103	10
M12-1.25	1D	28122	10
	1.5D	28123	10
M14-1.25	3/8"	28148	10
	7/16"	28147	10
	1/2"	28149	10
	3/4"	28140	10
	8.4mm	28140-8.4	5
M14-1.25	12.4mm	28140-12.4	5
	16.4mm	28140-16.4	5
M18-1.50	7mm	28189	5

左ねじ用	長さ	部品番号	入数
M6-1.00	1.5D	25063LH	10
M8-1.25	1.5D	25083LH	10
M10-1.50	1.5D	25103LH	10
M10-1.25	1.5D	27103LH	10
M12-1.75	1.5D	25123LH	10

インコネル	長さ	部品番号	入数
M18-1.50	1.5D	28181X	5

