


SBI - HL形 / SBI - HLL形



単位：mm

型番	組立寸法				ブロック寸法												
	H	W	L	E	取付け穴				L1	T±1	K	T1	N1	T2	N2	Q1	※Q2
					B	J	M	DP									
SBI15HLS	24	34	56.8	3	26	26	M4	4	38.2	6	21	4.5	5.5	3.8	3.8	M4×0.7	Φ3.5
SBI15HL	24	34	63.8	3	26	26	M4	4	45.2	6	21	4.5	5.5	3.8	3.8	M4×0.7	Φ3.5
SBI15HLL	24	34	79.4	3	26	34	M4	4	60.8	6	21	4.5	5.5	3.8	3.8	M4×0.7	Φ3.5
SBI25HLS	36	48	83	5.5	35	35	M6	6	61	12	30.5	6	12	5	5.5	M6×0.75	Φ3.5
SBI25HL	36	48	92	5.5	35	35	M6	6	70	12	30.5	6	12	5	5.5	M6×0.75	Φ3.5
SBI25HLL	36	48	108	5.5	35	50	M6	6	86	12	30.5	6	12	5	5.5	M6×0.75	Φ3.5
SBI30HLS	42	60	96.8	7	40	40	M8	8	68.8	12	35	8.5	12	7.8	5	M6×0.75	Φ5.7
SBI30HL	42	60	107.6	7	40	40	M8	8	79.6	12	35	8.5	12	7.8	5	M6×0.75	Φ5.7
SBI30HLL	42	60	131.6	7	40	60	M8	8	103.6	12	35	8.5	12	7.8	5	M6×0.75	Φ5.7
SBI35HLS	48	70	108.2	8	50	50	M8	8	78.2	15	40.5	8	12	8	6	M6×0.75	Φ5.7
SBI35HL	48	70	124.6	7.5	50	50	M8	8	94.6	15	40.5	8	12	8	6	M6×0.75	Φ5.7
SBI35HLL	48	70	152.6	7.5	50	72	M8	8	122.6	15	40.5	8	12	8	6	M6×0.75	Φ5.7
SBI45HL	60	86	142	9	60	60	M10	10	108	17	51	10.5	13.5	9.3	6.5	PT1/8	Φ5.7
SBI45HLL	60	86	174	9	60	80	M10	10	140	17	51	10.5	13.5	9.3	6.5	PT1/8	Φ5.7
SBI55HL	70	100	172.4	12	75	75	M12	12	131	21	58	12	13	12	8	PT1/8	Φ8.7
SBI55HLL	70	100	211.8	12	75	95	M12	12	170.4	21	58	12	13	12	8	PT1/8	Φ8.7

※ Q2：側面ニップル取付用キリ穴です。