

六角ボルト(全ネジ)(細目)



B0000004

鉄

B0020004

ステンレス

M8.0

長さ	入り数	鉄										ステンレス
		生地	クロメート	クロム	亜鉛黒	亜鉛白	三価クロム	三価クロム	三価クロム	三価クロム	三価クロム	
15	200×10											●
15	350×8	●	●	●	●	●	●	●	●	●	●	●
16	350×8	●	●	●	●	●	●	●	●	●	●	●
20	200×10											●
20	300×8	●	●	●	●	●	●	●	●	●	●	●
25	200×10											●
25	250×8	●	●	●	●	●	●	●	●	●	●	●
30	100×10											●
30	200×8	●	●	●	●	●	●	●	●	●	●	●
35	180×8	●	●	●	●	●	●	●	●	●	●	●
40	100×10											●
40	150×8	●	●	●	●	●	●	●	●	●	●	●
50	100×10											●
50	130×8	●	●	●	●	●	●	●	●	●	●	●

M10.0

長さ	入り数	鉄										ステンレス
		生地	クロメート	クロム	亜鉛黒	亜鉛白	三価クロム	三価クロム	三価クロム	三価クロム	三価クロム	
15	100×10											●
15	200×6	●	●	●	●	●	●	●	●	●	●	●
16	100×10											●
16	180×8	●	●	●	●	●	●	●	●	●	●	●
18	180×8	●	●	●	●	●	●	●	●	●	●	●
20	100×12											●
20	150×8	●	●	●	●	●	●	●	●	●	●	●
22	200×5	●	●	●	●	●	●	●	●	●	●	●
25	100×12											●
25	140×8	●	●	●	●	●	●	●	●	●	●	●
30	100×9											●
30	120×8	●	●	●	●	●	●	●	●	●	●	●
35	100×8	●	●	●	●	●	●	●	●	●	●	●
35	100×9											●
40	100×8	●	●	●	●	●	●	●	●	●	●	●
45	100×7											●
45	90×8	●	●	●	●	●	●	●	●	●	●	●
50	100×6											●
50	75×8	●	●	●	●	●	●	●	●	●	●	●
55	100×10											●
55	75×8	●	●	●	●	●	●	●	●	●	●	●
60	100×10											●
60	65×8	●	●	●	●	●	●	●	●	●	●	●
65	50×10											●
65	60×8	●	●	●	●	●	●	●	●	●	●	●
70	100×10											●
70	60×8	●	●	●	●	●	●	●	●	●	●	●
75	50×10											●
75	60×8	●	●	●	●	●	●	●	●	●	●	●
80	100×1	●	●	●	●							●
80	100×10											●
90	100×5	●	●	●	●	●	●	●	●	●	●	●
90	50×10											●
100	100×10	●	●									●
100	100×5			●								●
100	50×10											●
110	50×1											●
120	50×1											●
130	50×1											●
140	50×1											●
150	50×1											●