

M24.0												
長さ	入り数	鉄										ステンレス
		生地	クロメ	クロメコート	三価ホワイト	三価ブラック	ニッケル	クロム	亜鉛黒	パーカー	ドブ	
70	1×85	●	●	●	●	●	●	●	●	●	●	●
70	15×6											●
75	1×85	●	●	●	●	●	●	●	●	●	●	●
75	15×5											●
80	1×80	●	●	●	●	●	●	●	●	●	●	●
80	15×5											●
85	1×75	●	●	●	●	●	●	●	●	●	●	●
85	15×5											●
90	1×75	●	●	●	●	●	●	●	●	●	●	●
90	10×6											●
95	1×70	●	●	●	●	●	●	●	●	●	●	●
95	10×6											●
100	1×70	●	●	●	●	●	●	●	●	●	●	●
100	10×6											●
110	1×60	●	●	●	●	●	●	●	●	●	●	●
110	10×6											●
120	1×55	●	●	●	●	●	●	●	●	●	●	●
120	10×6											●
130	1×55	●	●	●	●	●	●	●	●	●	●	●
130	10×5											●
140	1×50	●	●	●	●	●	●	●	●	●	●	●
140	10×5											●
150	1×45	●	●	●	●	●	●	●	●	●	●	●
150	10×5											●
160	10×4											●
170	10×4											●
180	10×4											●
190	10×4											●
200	8×4											●

M30.0					
長さ	入り数	鉄			ステンレス
		生地	クロメ	クロメコート	
80	1×50	●	●	●	
80	10×4				●
85	1×45	●	●	●	
85	10×4				●
90	1×45	●	●	●	
90	8×4				●
95	1×45	●	●	●	
95	8×4				●
100	1×40	●	●	●	
100	8×4				●
105	1×40	●	●	●	
110	1×40	●	●	●	
110	8×4				●
115	1×35	●	●	●	
120	1×35	●	●	●	
120	7×4				●
125	1×35	●	●	●	
130	1×30	●	●	●	
130	7×4				●
140	1×30	●	●	●	
140	7×4				●
150	1×30	●	●	●	
150	6×4				●
160	1×30	●	●	●	
160	6×4				●
170	1×30	●	●	●	
170	6×4				●
180	1×25	●	●	●	
180	6×4				●
190	1×25	●	●	●	
190	5×4				●
200	1×25	●	●	●	
200	5×4				●
210	1×20	●	●	●	
220	1×20	●	●	●	
230	1×20	●	●	●	
240	1×20	●	●	●	
250	1×20	●	●	●	

鉄 六角ボルト(全ねじ)金剛鋌螺製



B000K000
鉄

M3.0										
長さ	入り数	鉄								
		生地	クロメ	クロメコート	三価ホワイト	三価ブラック	ニッケル	クロム	亜鉛黒	パーカー
8	4000×10	●	●	●	●	●	●	●	●	●
10	3000×12	●	●	●	●	●	●	●	●	●
12	3000×10	●	●	●	●	●	●	●	●	●
14	3000×10	●	●	●	●	●	●	●	●	●
15	2500×10	●	●	●	●	●	●	●	●	●
16	2500×10	●	●	●	●	●	●	●	●	●
18	2000×10	●	●	●	●	●	●	●	●	●
20	2000×10	●	●	●	●	●	●	●	●	●
25	2000×9	●	●	●	●	●	●	●	●	●

M4.0										
長さ	入り数	鉄								
		生地	クロメ	クロメコート	三価ホワイト	三価ブラック	ニッケル	クロム	亜鉛黒	パーカー
8	1500×12	●	●	●	●	●	●	●	●	●
10	1500×12	●	●	●	●	●	●	●	●	●
12	1500×12	●	●	●	●	●	●	●	●	●
14	1500×10	●	●	●	●	●	●	●	●	●
15	1500×10	●	●	●	●	●	●	●	●	●
16	1500×10	●	●	●	●	●	●	●	●	●
18	1500×10	●	●	●	●	●	●	●	●	●
20	1500×9	●	●	●	●	●	●	●	●	●
22	1000×10	●	●	●	●	●	●	●	●	●
25	1000×10	●	●	●	●	●	●	●	●	●
30	1000×9	●	●	●	●	●	●	●	●	●
35	1000×8	●	●	●	●	●	●	●	●	●
40	1000×7	●	●	●	●	●	●	●	●	●
45	800×7	●	●	●	●	●	●	●	●	●
50	700×7	●	●	●	●	●	●	●	●	●

M5.0										
長さ	入り数	鉄								
		生地	クロメ	クロメコート	三価ホワイト	三価ブラック	ニッケル	クロム	亜鉛黒	パーカー
6	1000×13	●	●	●	●	●	●	●	●	●
8	1000×12	●	●	●	●	●	●	●	●	●
10	1000×12	●	●	●	●	●	●	●	●	●
12	1000×12	●	●	●	●	●	●	●	●	●
14	1000×10	●	●	●	●	●	●	●	●	●
15	1000×10	●	●	●	●	●	●	●	●	●
16	1000×10	●	●	●	●	●	●	●	●	●
18	1000×9	●	●	●	●	●	●	●	●	●
20	1000×9	●	●	●	●	●	●	●	●	●
25	1000×8	●	●	●	●	●	●	●	●	●
30	500×10	●	●	●	●	●	●	●	●	●
35	500×9	●	●	●	●	●	●	●	●	●
40	500×9	●	●	●	●	●	●	●	●	●
45	500×8	●	●	●	●	●	●	●	●	●
50	500×7	●	●	●	●	●	●	●	●	●

小ねじ
マフロねじ
組込みねじ
タツピンねじ
タツタイト
ハイタクねじ
いたすら防止ねじ
建材用スクリュー
ドリルねじ
座金
つまみねじ
ナット
樹脂製品
アンカーボルト