

小ねじ
マフクロねじ
組込みねじ
タッピンねじ
タツプタイト・
ハイテックねじ
いたすら防止ねじ
建材用スクリーン
ボルト
キャップホーロー
ドリルねじ
座金
つまみねじ
ナット
樹脂製品
アンカーボルト

鋼 8マーク小型六角ボルト (半ねじ)



B0008510

鉄

M8.0										
長さ	入り数	生地	クロメート	クロメート	三価ホウ酸	ニッケル	クロム	亜鉛黒	ダクロ	グリーン
30	200×10	●	●	●	●	●	●	●	●	●
35	200×9	●	●	●	●	●	●	●	●	●
40	200×8	●	●	●	●	●	●	●	●	●
45	200×8	●	●	●	●	●	●	●	●	●
50	200×7	●	●	●	●	●	●	●	●	●
55	200×7	●	●	●	●	●	●	●	●	●
60	200×6	●	●	●	●	●	●	●	●	●
65	200×6	●	●	●	●	●	●	●	●	●
70	100×9	●	●	●	●	●	●	●	●	●
75	100×9	●	●	●	●	●	●	●	●	●
80	100×9	●	●	●	●	●	●	●	●	●
85	100×8	●	●	●	●	●	●	●	●	●
90	100×8	●	●	●	●	●	●	●	●	●
95	100×7	●	●	●	●	●	●	●	●	●
100	100×7	●	●	●	●	●	●	●	●	●

M10.0										
長さ	入り数	生地	クロメート	クロメート	三価ホウ酸	ニッケル	クロム	亜鉛黒	ダクロ	グリーン
30	200×6	●	●	●	●	●	●	●	●	●
35	200×6	●	●	●	●	●	●	●	●	●
40	100×10	●	●	●	●	●	●	●	●	●
45	100×9	●	●	●	●	●	●	●	●	●
50	100×8	●	●	●	●	●	●	●	●	●

鋼 8マーク小型六角ボルト (半ねじ) (細目)



B0008514

鉄

M10.0										
長さ	入り数	生地	クロメート	クロメート	三価ホウ酸	ニッケル	クロム	亜鉛黒	ダクロ	グリーン
30	200×8	●	●	●	●	●	●	●	●	●
35	200×6	●	●	●	●	●	●	●	●	●
40	100×10	●	●	●	●	●	●	●	●	●
45	100×9	●	●	●	●	●	●	●	●	●
50	100×8	●	●	●	●	●	●	●	●	●
55	100×8	●	●	●	●	●	●	●	●	●
60	100×7	●	●	●	●	●	●	●	●	●
65	100×7	●	●	●	●	●	●	●	●	●
70	100×6	●	●	●	●	●	●	●	●	●
75	100×6	●	●	●	●	●	●	●	●	●
80	100×6	●	●	●	●	●	●	●	●	●
85	60×6	●	●	●	●	●	●	●	●	●
90	90×6	●	●	●	●	●	●	●	●	●
95	50×6	●	●	●	●	●	●	●	●	●
100	80×6	●	●	●	●	●	●	●	●	●

M12.0										
長さ	入り数	生地	クロメート	クロメート	三価ホウ酸	ニッケル	クロム	亜鉛黒	ダクロ	グリーン
35	100×7	●	●	●	●	●	●	●	●	●
40	100×7	●	●	●	●	●	●	●	●	●
45	100×6	●	●	●	●	●	●	●	●	●
50	100×6	●	●	●	●	●	●	●	●	●
55	50×10	●	●	●	●	●	●	●	●	●
60	50×9	●	●	●	●	●	●	●	●	●
65	50×8	●	●	●	●	●	●	●	●	●
70	50×8	●	●	●	●	●	●	●	●	●
75	50×8	●	●	●	●	●	●	●	●	●
80	50×8	●	●	●	●	●	●	●	●	●
85	40×6	●	●	●	●	●	●	●	●	●
90	50×7	●	●	●	●	●	●	●	●	●
95	50×7	●	●	●	●	●	●	●	●	●
100	50×7	●	●	●	●	●	●	●	●	●
110	50×6	●	●	●	●	●	●	●	●	●
120	40×6	●	●	●	●	●	●	●	●	●
130	40×6	●	●	●	●	●	●	●	●	●
140	40×6	●	●	●	●	●	●	●	●	●
150	40×6	●	●	●	●	●	●	●	●	●

M14.0										
長さ	入り数	生地	クロメート	クロメート	三価ホウ酸	ニッケル	クロム	亜鉛黒	ダクロ	グリーン
45	70×6	●	●	●	●	●	●	●	●	●
50	60×6	●	●	●	●	●	●	●	●	●
55	50×7	●	●	●	●	●	●	●	●	●
60	50×7	●	●	●	●	●	●	●	●	●
65	40×6	●	●	●	●	●	●	●	●	●
70	50×6	●	●	●	●	●	●	●	●	●
75	40×6	●	●	●	●	●	●	●	●	●
80	40×6	●	●	●	●	●	●	●	●	●
85	40×6	●	●	●	●	●	●	●	●	●
90	30×6	●	●	●	●	●	●	●	●	●
95	30×6	●	●	●	●	●	●	●	●	●
100	25×6	●	●	●	●	●	●	●	●	●
110	30×6	●	●	●	●	●	●	●	●	●
120	25×6	●	●	●	●	●	●	●	●	●
130	25×6	●	●	●	●	●	●	●	●	●
140	25×6	●	●	●	●	●	●	●	●	●
150	20×6	●	●	●	●	●	●	●	●	●

M16.0										
長さ	入り数	生地	クロメート	クロメート	三価ホウ酸	ニッケル	クロム	亜鉛黒	ダクロ	グリーン
45	50×6	●	●	●	●	●	●	●	●	●
50	50×6	●	●	●	●	●	●	●	●	●
55	50×6	●	●	●	●	●	●	●	●	●
60	45×6	●	●	●	●	●	●	●	●	●
65	45×6	●	●	●	●	●	●	●	●	●
70	30×6	●	●	●	●	●	●	●	●	●
75	40×6	●	●	●	●	●	●	●	●	●
80	40×6	●	●	●	●	●	●	●	●	●
85	40×6	●	●	●	●	●	●	●	●	●
90	25×6	●	●	●	●	●	●	●	●	●
95	30×7	●	●	●	●	●	●	●	●	●
100	20×6	●	●	●	●	●	●	●	●	●
110	30×6	●	●	●	●	●	●	●	●	●
120	30×6	●	●	●	●	●	●	●	●	●
130	30×4	●	●	●	●	●	●	●	●	●
140	30×4	●	●	●	●	●	●	●	●	●
150	30×6	●	●	●	●	●	●	●	●	●