

丸ワッシャー (特寸)



W0000060

鉄

W0010060

黄銅

W0020060

ステンレス

W0110060

SUS 316

W0060060

アルミ

特長

●相手が木材の場合、外径の大きい木材用丸ワッシャーを使用することで陥没を防ぎます。

呼び	入り数	鉄													黄銅		ステンレス			SUS316	アルミ	
		生地	クロメート	三価ホフイ	三価フタク	ニッケル	クロム	GBフタロ	亜鉛黒	パーカー	ドブ	ダクロ	グリーン	ステンコート	ステンバルト	黒ツアル	銅メッキ	生地	ニッケル	生地	GBフタロ	GBフタロ
1.05×3×0.2	10000×20																					
2×6×0.3	20000×10																	●	●			
2.2×6×0.8	10000×20																			●	●	●
3×6×0.3	20000×10																	●	●			
3×6×1.0	20000×10	●	●	●	●	●							●		●	●						
3×8×0.8	15000×10	●	●	●	●	●							●		●	●						
3×10×0.5	10000×10	●	●	●	●								●					●	●			
3×10×0.8	5000×10																	●	●			
3×10×0.8	8000×10		●	●	●	●							●									
3×10×0.8	8000×10																			●	●	●
3×10×1.0	7000×10		●	●	●	●							●		●							
3×12×0.8	5000×10																			●	●	●
3×12×0.8	6000×10		●	●	●	●							●		●	●						
3×12×1.0	4000×10		●	●	●	●							●		●	●						
3×14×1.0	3000×10																			●	●	●
3.2×10×1.2	3000×10		●	●	●	●							●		●	●						
3.2×10×1.6	2000×10	●	●	●	●	●							●		●	●						
3.2×13×1.2	3000×8																			●	●	●
3.3×6×0.4	10000×10		●	●	●										●	●						
3.3×6×0.5	1000×20																					●
3.3×8×0.3	10000×10																			●	●	●
3.3×8×1.0	5000×10																			●	●	●
3.3×9×1.0	4000×10	●	●	●	●	●							●		●	●						
3.3×10×0.5	7000×10																			●	●	●
3.3×10×1.5	2000×10																			●	●	●
3.3×12×1.2	2000×10		●	●	●	●							●		●	●						
3.3×12×1.6	1600×10	●	●	●	●	●							●									
3.3×13×1.0	2000×10		●	●	●	●							●		●	●						
3.3×15×1.0	1500×10																			●	●	●
3.3×16×1.0	1500×10	●	●	●	●	●							●		●	●						
3.3×17×1.6	2000×10		●	●	●	●							●		●	●						
3.4×8×1.0	10000×10		●		●	●							●		●	●						
3.4×20×1.0	900×10																			●	●	●
3.5×10×1.0	5000×10																			●		
3.5×12×0.5	5000×10		●	●	●	●							●		●	●						
4×8×0.3	20000×10																	●	●			
4×10×0.5	10000×10		●	●	●								●		●			●	●			
4×10×1.0	7000×10	●	●	●	●	●							●		●	●				●	●	●
4×12×0.8	6000×10	●	●	●	●	●							●		●	●				●	●	●
4×12×1.0	5000×10																			●	●	●
4×12×1.0	5000×10	●	●	●	●	●							●									
4×13×1.2	3000×10		●	●	●	●							●		●	●						
4×14×0.8	4000×10	●	●	●	●	●							●									
4×14×1.0	3000×10																			●	●	●
4×14×1.0	3000×10		●	●	●	●							●		●	●						
4×16×0.8	3000×10		●	●	●	●							●		●	●				●	●	●
4×16×1.0	2500×10		●	●	●	●							●		●	●						
4×16×1.6	1500×10	●	●	●	●	●							●		●	●						
4×18×1.6	1200×10		●	●	●	●							●		●	●						
4×20×1.0	1500×10	●	●	●	●	●							●		●	●						
4.1×6×0.5	10000×10																	●				
4.1×10×0.8	10000×10																			●		
4.3×8×1.2	10000×10																			●		
4.3×13×3.0	800×10	●	●	●	●																	
4.5×8×0.3	10000×10		●	●	●								●		●	●						
4.5×10×0.5	7000×10																			●	●	●
4.5×10×1.2	3000×10		●	●	●	●							●		●	●						