

割ピン



D0000000	D0010000	D0070000	D0020000	D0110000	D0120000
鉄	黄銅	銅	ステンレス	SUS 316	SUS 316L



呼び径		0.6	0.8	1	1.2	1.6	2	2.5	3.2	4	5	6.3	8	10	13	16	20	
d	基準寸法	0.5	0.7	0.9	1	1.4	1.8	2.3	2.9	3.7	4.6	5.9	7.5	9.5	12.4	15.4	19.3	
	許容差	0 -0.1						0 -0.2						0 -0.3				
c	基準寸法	1	1.4	1.8	2	2.8	3.6	4.6	5.8	7.4	9.2	11.8	15	19	24.8	30.8	38.6	
	許容差	0 -0.1	0 -0.2		0 -0.3	0 -0.4		0 -0.6	0 -0.7	0 -0.9	0 -1.2	0 -1.5	0 -1.9	0 -2.4	0 -3.1	0 -3.8	0 -4.8	
b		約	2	2.4	3	3	3.2	4	5	6.4	8	10	12.6	16	20	26	32	40
a		最大	1.6	1.6	1.6	2.5	2.5	2.5	2.5	3.2	4	4	4	4	6.3	6.3	6.3	6.3
		最小	0.8	0.8	0.8	1.2	1.2	1.2	1.2	1.6	2	2	2	2	3.2	3.2	3.2	3.2
適用する ボルト及び ピンの径	ボルト	を越え	—	2.5	3.5	4.5	5.5	7	9	11	14	20	27	39	56	80	120	170
		以下	2.5	3.5	4.5	5.5	7	9	11	14	20	27	39	56	80	120	170	—
	クレビス ピン	を越え	—	2	3	4	5	6	8	9	12	17	23	29	44	69	110	160
		以下	2	3	4	5	6	8	9	12	17	23	29	44	69	110	160	—
ピン穴径		(参考)	0.6	0.8	1	1.2	1.6	2	2.5	3.2	4	5	6.3	8	10	13	16	20

0.8				
長さ	入り数	鉄	黄銅	ステンレス
6	1000×40			●
6	5000×30	●		
8	1000×40			●
8	5000×30	●		
10	1000×40		●	●
10	5000×30	●		
12	1000×40			●
12	5000×30	●		
15	1000×40		●	●
15	5000×30	●		
18	1000×40			●
20	1000×40			●
25	1000×40			●
30	1000×40			●

1.0						
長さ	入り数	鉄	黄銅	ステンレス	SUS 316	SUS 316L
6	1000×40			●	●	
6	5000×30	●				
8	1000×40			●	●	
8	5000×30	●	●			
10	1000×40					●
10	5000×30	●	●	●		
12	1000×40			●	●	
12	5000×30	●	●			
15	1000×40			●	●	
15	2000×30					●
18	1000×40					●
18	5000×30	●	●			
20	1000×40			●	●	
20	2000×30					●
25	1000×40			●	●	
25	2000×30					●
30	1000×40					●
30	2000×30					●

1.2						
長さ	入り数	鉄	黄銅	ステンレス	SUS 316	SUS 316L
6	1000×40			●		
6	5000×30	●				
8	1000×40			●	●	
8	5000×30	●	●	●		
10	1000×40			●	●	
10	2000×30					●
12	1000×40			●	●	
12	2000×30					●
15	1000×40			●	●	
15	2000×30					●
18	1000×40			●	●	
18	2000×30					●
20	1000×40			●	●	
20	2000×30					●
25	1000×40			●	●	
25	2000×30					●
30	1000×40			●	●	
30	2000×30					●

1.6						
長さ	入り数	鉄	黄銅	ステンレス	SUS 316	SUS 316L
5	2000×40	●				
6	4000×25	●				
8	1000×40			●	●	
8	2000×30	●	●	●		
10	1000×40			●	●	
10	2000×30	●	●	●		
12	1000×40			●	●	
12	2000×30	●	●	●		
15	1000×40			●	●	
15	2000×30	●	●	●		
16	2000×8			●		
18	1000×40			●	●	
18	2000×30	●	●	●		
20	1000×30			●	●	
20	2000×30	●	●	●		
22	2000×30			●	●	
25	1000×30			●	●	
25	2000×20	●	●	●		
25	2000×30			●	●	
30	1000×30			●	●	
30	2000×20	●	●	●		
30	2000×30			●	●	
35	1000×30			●	●	
35	2000×14	●	●	●		
40	1000×20			●	●	
40	2000×14	●	●	●		
40	2000×30			●	●	
45	1000×20			●	●	
45	2000×30			●	●	
50	1000×20			●	●	
50	2000×14	●	●	●		
50	2000×30			●	●	