


⊕ 皿小ねじ



00000001	00010001	00020001	00120001	00170001	00060001	00090001
鉄	黄銅	ステンレス	SUS 316L	SUS 430	アルミ	チタン



ねじの呼び	ピッチ	十字穴の番号	dk		k		c	m	q(十字穴深さ)	
			基準寸法	許容差	基準寸法	許容差			約	参考
M2	0.4	1	4	0 -0.4	1.2	0 -0.2	0.2	2.2	1.01	0.65
M2.3	0.4		4.6		1.35		0.2	2.4	1.21	0.85
M2.5	0.45		5		1.45		0.2	2.6	1.42	1.05
M2.6	0.45		5.2		1.5		0.2	2.6	1.42	1.05
M3	0.5	2	6	0 -0.5	1.75	0 -0.3	0.25	3.6	1.43	0.91
M3.5	0.6		7		2		0.25	4.1	1.93	1.40
M4	0.7		8		2.3		0.3	4.5	2.33	1.79
M5	0.8		10		2.8		0.3	5.1	2.93	2.38
M6	1.0	3	12	0 -0.7	3.4	0 -0.4	0.4	6.7	3.26	2.70
M8	1.25		16		4.4		0.4	8.4	4.96	4.36
M10	1.5	4	20	0 -1.3	5.7	0 -0.5	0.7	10	5.95	5.15

		M2.0															
長さ	入り数	材質															
		鉄	黄銅				ステンレス				チタン						
		普通	ロクロ	ステンレス	チタン	黄銅	黄銅	黄銅	黄銅	ステンレス	ステンレス	ステンレス	ステンレス	チタン	チタン	チタン	チタン
2.5	15000×20																
3	10000×20																
3	10000×24																
3	13000×20																
3	15000×20																
4	10000×20																
4	10000×24																
4	12000×20																
5	10000×18																
5	10000×20																
5	10000×24																
6	10000×18																
6	8000×20																
6	9000×20																
7	7000×20																
7	8000×18																
8	7000×20																
8	8000×18																
9	6000×18																
10	5000×20																
10	6000×18																
11	6000×18																
12	4000×20																
12	6000×18																
14	3000×20																
14	3500×20																
14	4000×18																
15	3000×20																
15	4000×18																
16	2500×20																
16	3000×18																
16	3000×20																
18	2500×20																
18	3000×18																
20	2000×20																
20	3000×18																
25	1500×20																
25	2000×18																
30	1000×20																
30	1000×24																
35	1000×20																
40	700×20																

小ねじ
 マスチックねじ
 組込みねじ
 タンデムねじ
 タンクねじ
 ハイテックねじ
 いたずら防止ねじ
 建材用スクリュー
 ボルト
 キヤンブホーター
 ドリルねじ
 座金
 つまみねじ
 ナット
 樹脂製品
 アンカーボルト