

# ばね座金(スプリングワッシャー)2号 東京メタル製



W100000A	W104000A	W102000A	W112000A
鉄	焼青銅	ステンレス	SUS 316L

呼び	入り数	材質				
		鉄	焼青銅	ステンレス	SUS 316L	SUS 304
1/4	2500×5		●	●	●	●
3/8	1000×5		●	●	●	●
7/16	700×5		●	●	●	●
1/2	500×5		●	●	●	●
3/4	150×5		●	●	●	●
1"	70×5		●	●	●	●
1 1/8	50×5		●	●	●	●
1 1/4	40×5		●	●	●	●
1 3/8	30×5		●	●	●	●
M1	1000×100		●	●	●	●
M1.2	1000×100		●	●	●	●
M1.4	1000×100		●	●	●	●
M1.4	1000×10	●	●	●	●	●
M1.7	1000×100		●	●	●	●
M1.7	1000×10		●	●	●	●
M1.7	10000×5	●	●	●	●	●
M2	10000×24		●	●	●	●
M2	60000×5		●	●	●	●
2"	15×5		●	●	●	●
M2.3	10000×24		●	●	●	●
M2.3	50000×5		●	●	●	●
M2.5	10000×24		●	●	●	●
M2.5	40000×5		●	●	●	●
M2.6	10000×24		●	●	●	●
M2.6	40000×5		●	●	●	●
M3	10000×24		●	●	●	●
M3	30000×5		●	●	●	●
M3.5	10000×24		●	●	●	●
M3.5	20000×5		●	●	●	●
M4	14000×5		●	●	●	●

呼び	入り数	材質				
		鉄	焼青銅	ステンレス	SUS 316L	SUS 304
M4	4000×24		●	●	●	●
M4.5	10000×5		●	●	●	●
M4.5	4000×24		●	●	●	●
M5	2000×24		●	●	●	●
M5	7000×5		●	●	●	●
M6	1000×24		●	●	●	●
M6	3000×5		●	●	●	●
M7	2500×5		●	●	●	●
M8	1500×5		●	●	●	●
M10	900×5		●	●	●	●
M12	550×5		●	●	●	●
M14	350×5		●	●	●	●
M16	250×5		●	●	●	●
M18	200×5		●	●	●	●
M20	140×5		●	●	●	●
M22	100×5		●	●	●	●
M24	80×5		●	●	●	●
M27	60×5		●	●	●	●
M30	45×5		●	●	●	●
M33	40×5		●	●	●	●
M36	25×5		●	●	●	●
M39	25×5		●	●	●	●
M42	20×5		●	●	●	●
M45	20×5		●	●	●	●
M48	15×5		●	●	●	●
M52	15×5		●	●	●	●
M56	15×5		●	●	●	●
M60	10×5		●	●	●	●
M64	10×5		●	●	●	●
M68	10×5		●	●	●	●

呼び	メートル ねじ用	ウィット ねじ用	基準 寸法	許容差	内径(d)		外径 (D)	幅(b)×厚さ(t) (最小)
					2号	2号		
2	-	2.1	+0.25 -0	4.4	0.9×0.5			
2.3	-	2.4		4.9	1.0×0.6			
2.5	-	2.6		5.2	1.0×0.6			
2.6	-	2.7	+0.3 0	5.3	1.0×0.6			
3	-	3.1		5.9	1.1×0.7			
(3.5)	-	3.6		6.6	1.2×0.8			
4	-	4.1		7.6	1.4×1.0			
5	-	5.1	+0.4 0	9.2	1.7×1.3			
6	-	6.1		12.2	2.7×1.5			
-	(1/4)	6.5		12.8	2.8×1.6			
(7)	-	7.1		13.4	2.8×1.6			
8	(5/16)	8.2	+0.5 0	15.4	3.2×2.0			
-	3/8	9.8		17.8	3.6×2.4			
10	-	10.2		18.4	3.7×2.5			
-	(7/16)	11.4		20.2	4.0×2.8			
12	-	12.2	+0.6 0	21.5	4.2×3.0			
-	1/2	13		22.7	4.4×3.2			
(14)	-	14.2		24.5	4.7×3.5			
16	5/8	16.2	+0.8 0	28	5.2×4.0			
(18)	-	18.2		31	5.7×4.6			
-	3/4	19.5		32.7	5.9×4.8			
20	-	20.2		33.8	6.1×5.1			
(22)	7/8	22.5	+1.0 0	37.7	6.8×5.6			
24	-	24.5		40.3	7.1×5.9			
-	1"	26		42.8	7.5×6.4			
(27)	-	27.5	+1.2 0	45.3	7.9×6.8			
-	1 1/8	29.3		47.9	8.3×7.1			
30	-	30.5		49.9	8.7×7.5			
-	1 1/4	32.5		52.7	9.1×7.9			
(33)	-	33.5	+1.4 0	54.7	9.5×8.2			
-	1 3/8	35.8		57.8	9.9×8.7			
36	-	36.5		59.1	10.2×9.0			
(39)	1 1/2	39.5		63.1	10.7×9.5			
42	-	42.5	+2.0 0	67	10.7×9.5			
45	-	46		70	10.7×9.5			
48	-	49		73	10.7×9.5			
52	-	53		80	12.0×10			
56	-	57		84	12.0×10			

小ねじ  
メッシュワッシャー  
組込みねじ  
タフロックねじ  
タフロックねじ  
ハイテックねじ  
いたすら防止ねじ  
建材用スクリーン  
ボルト  
キヤンブホーロー  
ドリルねじ  
座金  
つまみねじ  
ナット  
樹脂製品  
アーカーボルト