

寸切(荒先)



C1000500

鉄

C1020500

ステンレス

C1120500

SUS 316L

M3.0		
長さ	入り数	ステンレス
20	3000×6	●
25	2000×6	●
30	1500×6	●
35	1500×6	●
40	1500×6	●
45	1200×6	●
50	1200×6	●

M4.0										
長さ	入り数	鉄								ステンレス
		全長	1/2	1/3	1/4	1/5	1/6	1/8	1/10	
15	500×12	●	●	●	●	●	●	●	●	●
16	500×12	●	●	●	●	●	●	●	●	●
20	500×12	●	●	●	●	●	●	●	●	●
25	500×12	●	●	●	●	●	●	●	●	●
30	500×12	●	●	●	●	●	●	●	●	●
35	500×12	●	●	●	●	●	●	●	●	●
40	500×12	●	●	●	●	●	●	●	●	●
45	500×12	●	●	●	●	●	●	●	●	●
50	500×12	●	●	●	●	●	●	●	●	●
55	250×12	●	●	●	●	●	●	●	●	●
60	250×12	●	●	●	●	●	●	●	●	●
65	250×12	●	●	●	●	●	●	●	●	●
70	250×12	●	●	●	●	●	●	●	●	●
75	250×12	●	●	●	●	●	●	●	●	●
80	250×12	●	●	●	●	●	●	●	●	●
85	250×12	●	●	●	●	●	●	●	●	●
90	250×12	●	●	●	●	●	●	●	●	●
95	250×12	●	●	●	●	●	●	●	●	●
100	250×12	●	●	●	●	●	●	●	●	●
105	1×1									●
110	1×1		●							
110	500×6									●
110	600×3	●	●							
115	1×1									●
120	1×1		●							
120	500×6									●
120	600×3	●	●							
125	1×1									●
130	500×6									●
130	600×3	●	●							
135	1×1									●
140	1×1	●	●							
140	600×5									●
145	1×1									●
150	375×4	●	●	●						
150	600×5									●
160	375×4	●	●	●						
170	1×1	●	●	●						
180	375×4	●	●	●						
190	1×1	●	●	●						
200	350×4	●	●	●						
210	1×1	●	●	●						
220	1×1	●	●	●						
230	300×4	●	●	●						
240	1×1	●	●	●						
250	300×4	●	●	●						
260	250×4	●	●	●						
270	1×1	●	●	●						
280	1×1	●	●	●						
290	250×4	●	●	●						
300	250×4	●	●	●						
350	1×1	●	●	●						
400	1×1	●	●	●						
450	1×1	●	●	●						
500	1×1	●	●	●						
550	1×1	●	●	●						
600	1×1	●	●	●						

M5.0										
長さ	入り数	鉄								ステンレス
		全長	1/2	1/3	1/4	1/5	1/6	1/8	1/10	
15	250×12	●	●	●	●	●	●	●	●	●
20	250×12	●	●	●	●	●	●	●	●	●
25	250×12	●	●	●	●	●	●	●	●	●
30	250×12	●	●	●	●	●	●	●	●	●
35	250×12	●	●	●	●	●	●	●	●	●
40	250×12	●	●	●	●	●	●	●	●	●
45	250×12	●	●	●	●	●	●	●	●	●
50	250×12	●	●	●	●	●	●	●	●	●
55	150×12	●	●	●	●	●	●	●	●	●
60	150×12	●	●	●	●	●	●	●	●	●
65	150×12	●	●	●	●	●	●	●	●	●
70	150×12	●	●	●	●	●	●	●	●	●
75	150×12	●	●	●	●	●	●	●	●	●
80	150×12	●	●	●	●	●	●	●	●	●
85	150×12	●	●	●	●	●	●	●	●	●
90	150×12	●	●	●	●	●	●	●	●	●
95	150×12	●	●	●	●	●	●	●	●	●
100	150×12	●	●	●	●	●	●	●	●	●
105	1×1	●	●	●	●	●	●	●	●	●
110	1×1									●
110	375×4	●	●	●	●					
115	1×1	●	●	●	●	●	●	●	●	
120	1×1	●	●	●	●	●	●	●	●	
120	200×5									●
125	1×1	●	●	●	●	●	●	●	●	
125	200×5									●
130	250×4	●	●	●	●					
135	1×1	●	●	●	●	●	●	●	●	
140	250×4	●	●	●	●					
145	1×1	●	●	●	●	●	●	●	●	
150	250×4	●	●	●	●					
160	1×1	●	●	●	●	●	●	●	●	
170	250×4	●	●	●	●					
180	250×4	●	●	●	●					
190	250×4	●	●	●	●					
200	250×4	●	●	●	●					
210	1×1	●	●	●	●	●	●	●	●	
220	1×1	●	●	●	●	●	●	●	●	
230	1×1	●	●	●	●	●	●	●	●	
240	1×1	●	●	●	●	●	●	●	●	
250	1×1	●	●	●	●	●	●	●	●	
260	1×1	●	●	●	●	●	●	●	●	
270	1×1	●	●	●	●	●	●	●	●	
280	1×1	●	●	●	●	●	●	●	●	
290	1×1	●	●	●	●	●	●	●	●	
300	150×4	●	●	●	●					
350	1×1	●	●	●	●	●	●	●	●	
400	1×1	●	●	●	●	●	●	●	●	
450	1×1	●	●	●	●	●	●	●	●	
500	1×1	●	●	●	●	●	●	●	●	
550	1×1	●	●	●	●	●	●	●	●	
600	1×1	●	●	●	●	●	●	●	●	