


スミボロンインサート

刃先交換インサート

旋削用インサート

寸法(mm)






形状	型番	BN1000	BN2000	BNX20	BN350	BNX25	BNX10	BN500	BN7000	BN700	内接円 IC	厚さ S	コーナー半径 RE	穴径	適用ホルダ	Fig
		●	●					●	●							
 Fig 1	NU-ZNEX 040102 NU-ZNEX 040104 T-NU-ZNEX 040102 T-NU-ZNEX 040104	●	●					●	●		4.76	1.59	0.2	2.3	スミボロン 小径ボーリングバイト (BNZ 型) → L111	1 1 1 1
											4.76	1.59	0.4	2.3		
											4.76	1.59	0.2	2.3		
											4.76	1.59	0.4	2.3		

※ BNX25 は、NS 型(NS-ZNEX)でご用命ください。

※ T-NU-ZNEX は10 個入りアイテムです。




丸インサート

寸法(mm)

形状	型番	BN1000	BN2000	BNX20	BN350	BNX25	BNX10	BN500	BN7000	BN700	BNS800	内接円 IC	厚さ S	CBN 層厚さ S3	適用ホルダ	Fig
			●	●												
 Fig 1	RNGA 0906M0		●	●								9.00	6.35	0.80	スミボロン 丸インサートバイト (PRGN 型) → L114	1
 Fig 1	RNGN 120400-B								●	●		12.70	4.76	0.80	特殊ホルダ	1
	RNGN 150400-B											15.88	4.76	0.80		1
	RNGN 090300											9.525	3.18	3.18	ソリッド スミボロン用バイト (CRDN 型、CRSN 型) → L102	2
	RNGN 090300 LF											9.525	3.18	3.18		2
	RNGN 120300											12.70	3.18	3.18		2
	RNGN 120300 LF											12.70	3.18	3.18		2
RNGN 120400											12.70	4.76	4.76	2		
 Fig 1	RBG 08-B								●	●		8.00	6.50	0.80	スミボロン ロール加工用 丸駒バイト (BNRN 型) → L115	1
	RBG 10-B								●	●		10.00	9.00	0.80		1
	RBG 12-B								●	●		12.00	11.00	0.80		1
	RBG 16-B								●	●		16.00	13.00	0.80		1
	RBG 20-B								●	●		20.00	15.00	0.80		1
	RBG 26-B								●	●		26.00	15.00	0.80		1
 Fig 1	RCGA 0906M0		●									9.00	6.35	0.80	スミボロン 丸インサートバイト (PRGC 型、PRDC 型) → L114	1
 Fig 1	RTGN 0508M0			●								5.00	7.50	0.80	スミボロン 小径丸インサートバイト (TRGT 型) → L113	1
	RTGN 0608M0			●								6.00	7.50	0.80		1
	RTGN 0711M0			●								7.00	11.0	0.80		1
	RTGN 0811M0			●								8.00	11.0	0.80		1
	RTGN 0914M0			●								9.00	14.0	0.80		1
	RTGN 1014M0			●								10.00	14.0	0.80		1
	RTGN 1214M0			●								12.00	14.0	0.80		1

フライス用インサート

寸法(mm)

形状	型番	BN1000	BN2000	BN7000	BN700	内接円 IC	厚さ S	適用ホルダ	Fig
			●						
 Fig 1	CSN 43MT		●			12.70	4.76	SEC エースミル (DNF 型) → H48	1
 Fig 1	SNEN 1504ADTR			●	●	15.875	4.76	BN フィニッシュミル (FM 型、FMF 型) → L120	1
	SNEN 1504ADTL			●	●	15.875	4.76		1
	SNEN 1504ADTR-S			●	●	15.875	4.76		2
	SNEN 1504ADTL-S			●	●	15.875	4.76		2
 Fig 1	SNEW 1203ADTR			●	●	12.70	3.18	BN フィニッシュミル EASY (FMU 型) → L119	1
	SNEW 1203ADTR-S			●	●	12.70	3.18		2