

AC6020M/AC6030M/AC6135M/AC6145M

◇ ネガティブ 80° 菱形

形状	型番	在庫				寸法 (mm)			
		AC6020M	AC6030M	AC6135M	AC6145M	内接円	厚さ	穴径	コーナー半径
	CNMG 090304N-FE	●	●	●	●	9.525	3.18	3.81	0.4
	090308N-FE	●	●	●	●	9.525	3.18	3.81	0.8
	CNMG 090404N-FE	●	●	●	●	9.525	4.76	3.81	0.4
	090408N-FE	●	●	●	●	9.525	4.76	3.81	0.8
	CNMG 120402N-FE	●	●	●	●	12.7	4.76	5.16	0.2
	120404N-FE	●	●	●	●	12.7	4.76	5.16	0.4
	120408N-FE	●	●	●	●	12.7	4.76	5.16	0.8
	120412N-FE	●	●	●	●	12.7	4.76	5.16	1.2
	CNMG 090304N-LU	●	●	●	●	9.525	3.18	3.81	0.4
	090308N-LU	●	●	●	●	9.525	3.18	3.81	0.8
	CNMG 120402N-LU	●	●	●	●	12.7	4.76	5.16	0.2
	120404N-LU	●	●	●	●	12.7	4.76	5.16	0.4
	120408N-LU	●	●	●	●	12.7	4.76	5.16	0.8
	120412N-LU	●	●	●	●	12.7	4.76	5.16	1.2
	CNMG 120404N-LUW	●	●	●	●	12.7	4.76	5.16	0.4
	120408N-LUW	●	●	●	●	12.7	4.76	5.16	0.8
	120412N-LUW	●	●	●	●	12.7	4.76	5.16	1.2
	CNMG 120402N-SU	●	●	●	●	12.7	4.76	5.16	0.2
	120404N-SU	●	●	●	●	12.7	4.76	5.16	0.4
	120408N-SU	●	●	●	●	12.7	4.76	5.16	0.8
	120412N-SU	●	●	●	●	12.7	4.76	5.16	1.2
	CNMG 090404N-EF	●	●	●	●	9.525	4.76	3.81	0.4
	090408N-EF	●	●	●	●	9.525	4.76	3.81	0.8
	CNMG 120404N-EF	●	●	●	●	12.7	4.76	5.16	0.4
	120408N-EF	●	●	●	●	12.7	4.76	5.16	0.8
	120412N-EF	●	●	●	●	12.7	4.76	5.16	1.2
	CNMG 120404N-EX	●	●	●	●	12.7	4.76	5.16	0.4
	120408N-EX	●	●	●	●	12.7	4.76	5.16	0.8
	120412N-EX	●	●	●	●	12.7	4.76	5.16	1.2
	120416N-EX	●	●	●	●	12.7	4.76	5.16	1.6
	CNMG 160612N-EX	●	●	●	●	15.875	6.35	6.35	1.2
	CNMG 190612N-EX	●	●	●	●	19.05	6.35	7.94	1.2
	CNMG 120404N-UP	●	●	●	●	12.7	4.76	5.16	0.4
	120408N-UP	●	●	●	●	12.7	4.76	5.16	0.8
	120412N-UP	●	●	●	●	12.7	4.76	5.16	1.2
	CNMG 120404N-GU	●	●	●	●	12.7	4.76	5.16	0.4
	120408N-GU	●	●	●	●	12.7	4.76	5.16	0.8
	120412N-GU	●	●	●	●	12.7	4.76	5.16	1.2
	120416N-GU	●	●	●	●	12.7	4.76	5.16	1.6
	CNMG 160608N-GU	●	●	●	●	15.875	6.35	6.35	0.8
	160612N-GU	●	●	●	●	15.875	6.35	6.35	1.2
	160616N-GU	●	●	●	●	15.875	6.35	6.35	1.6
	CNMG 090408N-EG	●	●	●	●	9.525	4.76	3.81	0.8
	090412N-EG	●	●	●	●	9.525	4.76	3.81	1.2
	CNMG 120404N-EG	●	●	●	●	12.7	4.76	5.16	0.4
	120408N-EG	●	●	●	●	12.7	4.76	5.16	0.8
	120412N-EG	●	●	●	●	12.7	4.76	5.16	1.2
	CNMG 160608N-EG	●	●	●	●	15.875	6.35	6.35	0.8
	160612N-EG	●	●	●	●	15.875	6.35	6.35	1.2
	160616N-EG	●	●	●	●	15.875	6.35	6.35	1.6
	CNMG 190612N-EG	●	●	●	●	19.05	6.35	7.94	1.2
	190616N-EG	●	●	●	●	19.05	6.35	7.94	1.6
	CNMG 120408N-MU	●	●	●	●	12.7	4.76	5.16	0.8
	120412N-MU	●	●	●	●	12.7	4.76	5.16	1.2
	CNMG 160612N-MU	●	●	●	●	15.875	6.35	6.35	1.2
	160616N-MU	●	●	●	●	15.875	6.35	6.35	1.6
	CNMG 190612N-MU	●	●	●	●	19.05	6.35	7.94	1.2
	190616N-MU	●	●	●	●	19.05	6.35	7.94	1.6
	CNMG 120404N-EH	●	●	●	●	12.7	4.76	5.16	0.4
	120408N-EH	●	●	●	●	12.7	4.76	5.16	0.8
	120412N-EH	●	●	●	●	12.7	4.76	5.16	1.2
	120416N-EH	●	●	●	●	12.7	4.76	5.16	1.6
	CNMG 190612N-EH	●	●	●	●	19.05	6.35	7.94	1.2
	190616N-EH	●	●	●	●	19.05	6.35	7.94	1.6
	CNMG 120408N-EM	●	●	●	●	12.7	4.76	5.16	0.8
	120412N-EM	●	●	●	●	12.7	4.76	5.16	1.2
	120416N-EM	●	●	●	●	12.7	4.76	5.16	1.6
	CNMG 160608N-EM	●	●	●	●	15.875	6.35	6.35	0.8
	160612N-EM	●	●	●	●	15.875	6.35	6.35	1.2
	160616N-EM	●	●	●	●	15.875	6.35	6.35	1.6
	CNMG 190612N-EM	●	●	●	●	19.05	6.35	7.94	1.2
	190616N-EM	●	●	●	●	19.05	6.35	7.94	1.6
	190624N-EM	●	●	●	●	19.05	6.35	7.94	2.4
	CNMG 250924N-EM	●	●	●	●	25.4	9.52	9.12	2.4

◇ ネガティブ 80° 菱形

形状	型番	在庫				寸法 (mm)			
		AC6020M	AC6030M	AC6135M	AC6145M	内接円	厚さ	穴径	コーナー半径
	CNMM 120408N-MP	●	●	●	●	12.7	4.76	5.16	0.8
	120412N-MP	●	●	●	●	12.7	4.76	5.16	1.2
	120416N-MP	●	●	●	●	12.7	4.76	5.16	1.6
	CNMM 160608N-MP	●	●	●	●	15.875	6.35	6.35	0.8
	160612N-MP	●	●	●	●	15.875	6.35	6.35	1.2
	160616N-MP	●	●	●	●	15.875	6.35	6.35	1.6
	CNMM 190608N-MP	●	●	●	●	19.05	6.35	7.94	0.8
	190612N-MP	●	●	●	●	19.05	6.35	7.94	1.2
	190616N-MP	●	●	●	●	19.05	6.35	7.94	1.6
	190624N-MP	●	●	●	●	19.05	6.35	7.94	2.4