

ねじ

■ねじ

ダブルねじ (両穴)	型番	在庫	寸法 (mm)						(N·m)
			d	ピッチ	L	ℓ	D	B	
*WB4-8	●	M4	0.7	7.5	3	3.0	2	—	
WB5-10	●	M5	0.8	10	4	3.8	2.5	—	
WB5-12	●	M5	0.8	12	5	3.8	2.5	—	
WB6-10	●	M6	1.0	10	3.5	4.5	3	—	
WB6-13	●	M6	1.0	13	5	4.5	3	—	
WB6-16	●	M6	1.0	16	6	4.5	3	—	
WB6-20	●	M6	1.0	20	8.5	4.5	3	—	
WB6-30	●	M6	1.0	30	12	4.5	3	—	
WB6E-13	●	M6	1.0	13	5	4.5	2.78	—	
WB8-20	●	M8	1.25	20	8.5	6.2	4	—	
WB8-24	●	M8	1.25	24	8.5	6.2	4	—	
WB8-30	●	M8	1.25	30	11.5	6.2	4	—	
WB8F-20	●	M8	1.0	20	8.5	6.2	4	—	
WB8F-30	●	M8	1.0	30	11.5	6.2	4	—	
WB10-19	●	M10	1.5	19	8	7.9	5	—	
WB10-26	●	M10	1.5	26	11	7.9	5	—	
WB10-35	●	M10	1.5	35	13	7.9	5	—	

左ねじ 右ねじ

*: 左ねじ側のみレンチ穴あり。

ダブルねじ (トルクス穴)	型番	在庫	寸法 (mm)						(N·m)
			d	ピッチ	L	ℓ	D	B	
WB6-13T	●	M6	1.0	13	5	4.5	T20	—	
WB6-16T	●	M6	1.0	16	6	4.5	T20	—	
WB6-20T	●	M6	1.0	20	8.5	4.5	T20	—	
WB6-20TL	●	M6	1.0	20	8.5	4.5	T20	—	
WB7-15T	●	M7	1.0	15	5.5	5	T25	—	
WB7-20T	●	M7	1.0	20	8.5	5	T25	—	
WB7F-15T	●	M7	0.75	15	5.5	5	T25	—	
WB7F-20TL	●	M7	0.75	20	8.5	5.5	T25	—	
WB8-22T	●	M8	1.25	22	8.5	6.2	T27	—	
WB8-22TL	●	M8	1.25	22	8.5	6.2	T27	—	
WB8-30T	●	M8	1.25	30	11.5	6.2	T27	—	
WB8-30TL	●	M8	1.25	30	11.5	6.2	T27	—	
WB8R-16T	●	M8	1.25	14	5.5	6.2	T27	—	
WB8L-16T	●	M8	1.25	14	5.5	6.2	T27	—	

型番末尾T: 右ねじ, TL: 左ねじ
型番末尾TL: 左ねじ, T: 右ねじ

キャップスクリュー (六角穴つきボルト)	型番	在庫	寸法 (mm)						(N·m)
			d	ピッチ	L	ℓ	D	B	
BX0304	●	M3	0.5	4	全ネジ	5.5	2.5	—	
BX0308	●	M3	0.5	8	全ネジ	5.5	2.5	—	
BX0315	●	M3	0.5	15	全ネジ	5.5	2.5	—	
BX0320	●	M3	0.5	20	全ネジ	5.5	2.5	—	
BX0408	●	M4	0.7	8	全ネジ	7	3	—	
BX0410	●	M4	0.7	10	全ネジ	7	3	—	
BX0414	●	M4	0.7	14	全ネジ	7	3	—	
BX0425	●	M4	0.7	25	20	7	3	—	
BX0508	●	M5	0.8	8	全ネジ	8.5	4	—	
BX0510	●	M5	0.8	10	全ネジ	8.5	4	—	
BX0512	●	M5	0.8	12	全ネジ	8.5	4	—	
BX0515	●	M5	0.8	15	全ネジ	8.5	4	—	
BX0520	●	M5	0.8	20	全ネジ	8.5	4	5.0	
*BX0520T	●	M5	0.8	20	16	8.5	T20	—	
BX0610	●	M6	1.0	10	全ネジ	10	5	—	
BX0615	●	M6	1.0	15	全ネジ	10	5	—	
BX0620	●	M6	1.0	20	全ネジ	10	5	—	
BX0622	●	M6	1.0	22	18	10	5	—	
BX0625	●	M6	1.0	25	18	10	5	—	
BX0820	●	M8	1.25	20	全ネジ	13	6	—	
BX0830	●	M8	1.25	30	22	13	6	—	
BX0845	●	M8	1.25	45	13	6	—		
BX0850	●	M8	1.25	50	13	6	—		
BX1035	●	M10	1.5	35	26	16	8	—	
BX1060	●	M10	1.5	60	16	8	—		
BX1230	●	M12	1.75	30	全ネジ	18	10	—	
BX1260	●	M12	1.75	60	18	10	—		
BX1265	●	M12	1.75	66	18	10	—		
BX1660	●	M16	2.0	60	24	14	—		
BX2065	●	M20	2.5	65	30	17	—		
EHBX0512	●	M5	0.8	12	10.5	8	4	—	
*FADR	●	M7	1.0	10	7	10.5	T25	—	

*トルクス穴付

■ねじ

キャップスクリュー (トルクスプラス穴付き)	型番	在庫	寸法 (mm)						(N·m)
			d	ピッチ	L	ℓ	D	H	
BXA0310IP	●	M3	0.5	7.5	全ネジ	5.3	2.4	10IP	2.0

OH付キャップスクリュー	型番	在庫	寸法 (mm)						(N·m)
			d	ピッチ	L	ℓ	D	H	
BXH0825-D13	●	M8	1.25	25	全ネジ	13	8	6	—
BXH1030-D16	●	M10	1.5	30	全ネジ	16	10	8	—
BXH1235-D18	●	M12	1.75	35	全ネジ	18	12	10	—

OH付キャップスクリュー	型番	在庫	寸法 (mm)						(N·m)	
			d	ピッチ	L	ℓ	D	H1		
BXH1235-D33	●	M12	1.75	35	全ネジ	33	10	2	10	—
BXH1635-D40	●	M16	2.0	35	30	40	10	—	14	—
BXH2036-D50	●	M20	2.5	36	29	50	14	4	17	—

セットスクリュー (六角穴つき止めねじ)	型番	在庫	寸法 (mm)						(N·m)
			d	ピッチ	L	ℓ	D	B	
BTD0408	●	M4	0.7	8	2	2.8	2	—	
BTD0410	●	M4	0.7	10	2	2.8	2	—	
BTD0412	●	M4	0.7	12	2	2.8	2	—	
BTD0508	●	M5	0.8	8	2	3.5	2.5	—	
BTD05F09	●	M5	0.5	9	2	4	T15	—	
BTD0510	●	M5	0.8	10	3	3.5	2.5	—	
BTD0518	●	M5	0.8	18	4	3.5	2.5	—	
BTD0607	●	M6	1.0	7	2	4	3	—	
BTD0609	●	M6	1.0	9	2	4	3	—	
BTD0615	●	M6	1.0	15	5	4	3	—	
BTD0618	●	M6	1.0	18	5	4	3	—	
BTD0620	●	M6	1.0	20	5	4	3	—	
BTD0812	●	M8	1.25	12	2	5	4	—	
BTD0818	●	M8	1.25	18	6	5	4	—	
BTD0820	●	M8	1.25	20	6	5	4	—	
BTD0825	●	M8	1.25	25	8.5	5	4	—	
BTD0830	●	M8	1.25	30	10	5	4	—	
BTD0615T	●	M6	1.0	15	5	4.3	T20	—	
BTD0620T	▲	M6	1.0	20	5	4	T20	—	
BTD0825T	●	M8	1.25	25	8.5	5	T27	—	
BTD0830T	●	M8	1.25	30	10	5	T27	—	

トルクス穴

型番末尾のT (トルクス穴付)

ボタンねじ	型番	在庫	寸法 (mm)						(N·m)
			d	ピッチ	L	ℓ	D	B	
BH0304	●	M3	0.5	4	全ネジ	5.5	2	—	
BH0305	●	M3	0.5	5	全ネジ	5.5	2	—	
BH0306	●	M3	0.5	6	全ネジ	5.5	2	—	
FBUP3-A0-9 (BH0308相当)	●	M3	0.5	8	全ネジ	5.5	2	1.0	
BH0310	●	M3	0.5	10	全ネジ	5.5	2	—	
BH0315	●	M3	0.5	15	全ネジ	5.5	2	—	
BH03504	●	M3.5	0.6	4	全ネジ	7	2	—	
BH0408	●	M4	0.7	8	全ネジ	6	2.5	—	
BH0410T	●	M4	0.7	10	8	7.5	T15	—	
BH0415	●	M4	0.7	15	全ネジ	7.5	2.5	—	
BH0510	●	M5	0.8	10	全ネジ	9.5	3	—	
BH0516	●	M5	0.8	16	14.4	9.5	3	—	
BH0615	●	M6	1.0	15	全ネジ	10.5	4	—	
BH0616	●	M6	1.0	16	14	10.5	4	—	
BH0620	●	M6	1.0	20	全ネジ	10.5	4	—	
BH0824R	●	M8	1.25	24	20	12	4	—	
BH0824L	●	M8	1.25	24	20	12	4	—	
BH0825	●	M8	1.25	25	22.5	14	5	—	
BH0830R	●	M8	1.25	30	26	12	4	—	
BH0830L	●	M8	1.25	30	26	12	4	—	
BH0832	●	M8	1.25	32	29.5	14	5	—	
BH1030R	●	M10	1.5	30	26	14	5	—	
BH1030L	●	M10	1.5	30	26	14	5	—	
BH1036R	●	M10	1.5	36	32	14	5	—	
BH1036L	●	M10	1.5	36	32	14	5	—	

六角穴

トルクス穴

型番末尾のT (トルクス穴付)

★: ねじ側にも同一レンチ穴 (B) あり

★*: 左ねじを示す

部品他

N

部品

資 材
テックアルカニス