

呼び 호칭 Model	外径 외경(mm) Outer Dia.	内径 내경(mm) Inner Dia.	自由長 자유장(mm) Free length	定数 정수(kg/mm) spring constant	30万 (0.3million)		50万 (0.5 million)		100万 (1 million)	
					変形量 변형량(mm) Deflection	荷重 하중(kg) Load	変形量 변형량(mm) Deflection	荷重 하중(kg) Load	変形量 변형량(mm) Deflection	荷重 하중(kg) Load
SB 6×15	6	3	15	6.00	3.0	18	2.7	16	2.4	14
20			20	4.50	4.0		3.6			
25			25	3.60	5.0		4.5			
30			30	3.00	6.0		5.4			
35			35	2.60	7.0		6.3			
40			40	2.30	8.0		7.2			
45			45	2.00	9.0		8.1			
50			50	1.80	10.0		9.0			
55			55	1.60	11.0		9.9			
60			60	1.50	12.0		10.8			
65			65	1.38	13.0		11.7			
70	70	1.29	14.0	12.6						
SB 8×10	8	4	10	16.94	2.0	35	1.8	31	1.6	26
15			15	11.30	3.0		2.7			
20			20	8.47	4.0		3.6			
25			25	6.78	5.0		4.5			
30			30	5.65	6.0		5.4			
35			35	4.84	7.0		6.3			
40			40	4.24	8.0		7.2			
45			45	3.77	9.0		8.1			
50			50	3.39	10.0		9.0			
55			55	3.08	11.0		9.9			
60			60	2.82	12.0		10.8			
65			65	2.61	13.0		11.7			
70			70	2.42	14.0		12.6			
75			75	2.26	15.0		13.5			
80	80	2.12	16.0	14.4						
90	90	1.88	18.0	16.2						
SB 10×10	10	5	10	22.78	2.0	45	1.8	41	1.6	36
15			15	15.19	3.0		2.7			
20			20	11.25	4.0		3.6			
25			25	9.00	5.0		4.5			
30			30	7.50	6.0		5.4			
35			35	6.43	7.0		6.3			
40			40	5.63	8.0		7.2			
45			45	5.00	9.0		8.1			
50			50	4.50	10.0		9.0			
55			55	4.09	11.0		9.9			
60			60	3.75	12.0		10.8			
65			65	3.47	13.0		11.7			
70			70	3.21	14.0		12.6			
75			75	3.00	15.0		13.5			
80			80	2.82	16.0		14.4			
90			90	2.50	18.0		16.2			
100	100	2.25	20.0	18.0						