


● Material : Plated steel.
 ● 材質 : SS(三価クロメートメッキ)
 異径サイズもございますのでお問い合わせ下さい。

ストレートタイプアダプター

US-0609




接続口金具 : SR-02・SR-05

*印及びSUSは受注生産 ※ナットは36

呼び径	ねじT	Amm	Bmm	Lmm	dφmm	HEXmm
6	G ¼	13	8	38	5.5	19
9	G ⅜	15	8	42	7.0	22
12	G ½	18	10	50	10.0	27
19	G ¾	20	12	56	16.0	32*
25	G 1	22	12	60	22.0	41
* 32	G 1¼	25	14	68	28.0	50
* 38	G 1½	25	14	71	34.0	60
* 50	G 2	30	17	81	45.0	70

US-0613




接続口金具 : SR-02・SR-04

*印及びSUSは受注生産 ※ナットは36

呼び径	ねじT	Amm	Bmm	Lmm	dφmm	HEXmm
6	G ¼	16.0	8	41.0	5.5	19
9	G ⅜	17.5	8	44.5	7.0	22
12	G ½	20.0	10	52.0	10.0	27
19	G ¾	21.5	12	57.5	16.0	32*
25	G 1	22.5	12	60.5	22.0	41
* 32	G 1¼	27.0	14	71.0	28.0	50
* 38	G 1½	27.0	14	74.0	34.0	60
* 50	G 2	30.0	17	83.0	45.0	70

US-1609




接続口金具 : SR-05

*印及びSUSは受注生産

呼び径	ねじT	Amm	Bmm	Lmm	dφmm	HEXmm
6	G ¼	13	8	38	5.5	19
9	G ⅜	15	8	42	7.0	22
12	G ½	18	10	50	10.0	27
19	G ¾	20	12	56	16.0	36
25	G 1	22	12	60	22.0	41
* 32	G 1¼	24	14	68	28.0	50
* 38	G 1½	24	14	71	34.0	60
* 50	G 2	28	17	81	45.0	70

US-1613



接続口金具 : SR-04

*印及びSUSは受注生産 ※ナットは36

呼び径	ねじT	Amm	Bmm	Lmm	dφmm	HEXmm
6	G ¼	16.0	8	41.0	5.5	19
9	G ⅜	17.5	8	44.5	7.0	22
12	G ½	20.0	10	52.0	10.0	27
19	G ¾	21.5	12	57.5	16.0	32*
25	G 1	22.5	12	60.5	22.0	41
* 32	G 1¼	27.0	14	71.0	28.0	50
* 38	G 1½	27.0	14	74.0	34.0	60
* 50	G 2	30.0	17	83.0	45.0	70

(注意)予告なしに、改善(品質・性能・価格等)の為寸法等を変更する事がありますのでご了承ください。