




(mm)

形状	品番 (W.cut)	品番 (S.cut)	b	ℓ	L	メーカー希望 小売価格
	SB1A01	SB1A01S	1.5	6	38	1,490
	SB1A02	SB1A02S	2.5	11	38	1,490
	SB1A03	SB1A03S	3	14	38	1,490
	SB1A01E	SB1A01ES	3	14	38	1,490
	SB2A01	SB2A01S	2.5	11	38	1,490
	SB2A02	SB2A02S	3	14	38	1,490
	SB3A01	SB3A01S	3	12.7	38	1,490
	SB3A02	SB3A02S	3	6	38	1,490
	SB4A01	SB4A01S	3	9.5	38	1,490
	SB4A02	SB4A02S	3	6	38	1,490
	SB4A03	SB4A03S	3	12.7	38	1,490
	SB5A01	SB5A01S	3 ^{7°}	16	38	1,490
	SB5A02	SB5A02S	3 ^{12°}	8.9	38	1,490
	SB5A03	SB5A03S	3 ^{14°}	11	38	1,490
	SB6A01	SB6A01S	3	5.5	38	1,490
	SB7A01	SB7A01S	3 ^{8°}	12.7	38	1,490
	SB7A02	SB7A02S	3 ^{8°}	9.5	38	1,490
	SB8A01	SB8A01S	2.5	2.3	38	1,490
	SB8A02	SB8A02S	3	2.5	38	1,490
	SB49A01	SB49A01S	3 ^{90°}	1.5	38	1,490
	SB50A01	SB50A01S	3 ^{60°}	2.5	38	1,490
	SB51A01	SB51A01S	3	6.3	38	1,490
	SB52A01	SB52A01S	3 ^{10°}	4	38	1,490

(mm)

形状	品番 (W.cut)	品番 (S.cut)	b	ℓ	L	メーカー希望 小売価格
	SB1D01	SB1D01S	4	12.7	38	3,890
	SB1D02	SB1D02S	5	12.7	38	4,100
	SB2D03	SB2D03S	4	12.7	38	3,890
	SB2D04	SB2D04S	5	12.7	38	4,100
	SB3D08	SB3D08S	5	12.7	38	4,100
	SB4D09	SB4D09S	5	12.7	38	4,100
	SB5D12	SB5D12S	5 16°	12.7	38	4,100
	SB6D07	SB6D07S	5	7.1	38	4,100
	SB7D11	SB7D11S	5 14°	12.7	38	4,100
	SB8D05	SB8D05S	4	3.4	38	3,890
	SB8D06	SB8D06S	5	4.7	38	4,100
	SB51D10	SB51D10S	5	9.5	38	4,100
	SB52D13	SB52D13S	5 10°	6.3	38	4,100

(mm)

形状	品番 (W.cut)	品番 (S.cut)	b	ℓ	L	メーカー希望 小売価格
	SB1B01	SB1B01S	6.3	12.7	50	2,440
	SB1B02E	SB1B02ES	6.3	4.7	43	2,440
	SB2B03	SB2B03S	6.3	12.7	50	2,440
	SB3B06	SB3B06S	6.3	12.7	50	2,440
	SB4B07	SB4B07S	6.3	12.7	50	2,440
	SB5B08	SB5B08S	6.3 ^{22°}	12.7	54	2,440
	SB6B05	SB6B05S	6.3	9.5	47	2,440
	SB8B04	SB8B04S	6.3	5	44	2,440
	SB52B09	SB52B09S	6.3 ^{10°}	6	44	2,440