

TKHC56H33 ブラケット／仕切板 形番

販売終了

■ 仕切板

種類	仕切方式	形番
縦仕切板	縦仕切板のみ使用あるいはDSA	TKHC56H33SH-STAS
	DSB	TKHC56H33SH-STBS
横仕切板	DSA	TKHC56H33SH-HS〇〇
	DSB	TKHC56H33SH-HSB△△ TKHC56H33SH-EHS□□

〇〇＝本体W寸法

□□＝34～175 整数

■ 縦仕切板

形番	適用ケーブルベヤ本体
TKHC56H33SH-STAS	TKHC56H33SH**R**
TKHC56H33SH-STBS	
TKHC56H33SH-STBM	

■ 横仕切板（アルミニウム製）

形番	適用ケーブルベヤ本体
TKHC56H33SH-HS50	TKHC56H33SH50R**
TKHC56H33SH-HS75	TKHC56H33SH75R**
TKHC56H33SH-HS100	TKHC56H33SH100R**
TKHC56H33SH-HS125	TKHC56H33SH125R**
TKHC56H33SH-HS150	TKHC56H33SH150R**
TKHC56H33SH-HS175	TKHC56H33SH175R**
TKHC56H33SH-HS200	TKHC56H33SH200R**

■ 横仕切板（プラスチック製）

形番	適用ケーブルベヤ本体
TKHC56H33SH-HSB8	TKHC56H33SH**R**
TKHC56H33SH-HSB10	
TKHC56H33SH-HSB15	
TKHC56H33SH-HSB20	
TKHC56H33SH-HSB24	
TKHC56H33SH-HSB25	
TKHC56H33SH-HSB30	
TKHC56H33SH-HSB35	
TKHC56H33SH-HSB40	
TKHC56H33SH-HSB50	
TKHC56H33SH-HSB56	
TKHC56H33SH-HSB60	
TKHC56H33SH-HSB70	
TKHC56H33SH-HSB72	
TKHC56H33SH-HSB80	
TKHC56H33SH-HSB88	
TKHC56H33SH-HSB104	
TKHC56H33SH-HSB120	
TKHC56H33SH-HSB136	
TKHC56H33SH-HSB152	
TKHC56H33SH-HSB168	
TKHC56H33SH-HSB184	
TKHC56H33SH-HSB200	

■ エンドアダプタ付横仕切板

形番	適用ケーブルベヤ本体
TKHC56H33SH-EHS □□	TKHC56H33SH**R**

□□：34～175 整数

■ ブラケット

形番	適用ケーブルベヤ本体
TKHC56H33SH50-MU	TKHC56H33SH50R**
TKHC56H33SH50-FU	
TKHC56H33SH75-MU	TKHC56H33SH75R**
TKHC56H33SH75-FU	
TKHC56H33SH100-MU	TKHC56H33SH100R**
TKHC56H33SH100-FU	
TKHC56H33SH125-MU	TKHC56H33SH125R**
TKHC56H33SH125-FU	
TKHC56H33SH150-MU	TKHC56H33SH150R**
TKHC56H33SH150-FU	
TKHC56H33SH175-MU	TKHC56H33SH175R**
TKHC56H33SH175-FU	
TKHC56H33SH200-MU	TKHC56H33SH200R**
TKHC56H33SH200-FU	
TKHC56H33SH225-MU	TKHC56H33SH225R**
TKHC56H33SH225-FU	
TKHC56H33SH250-MU	TKHC56H33SH250R**
TKHC56H33SH250-FU	
TKHC56H33SH275-MU	TKHC56H33SH275R**
TKHC56H33SH275-FU	
TKHC56H33SH300-MU	TKHC56H33SH300R**
TKHC56H33SH300-FU	
TKHC56H33SH325-MU	TKHC56H33SH325R**
TKHC56H33SH325-FU	
TKHC56H33SH350-MU	TKHC56H33SH350R**
TKHC56H33SH350-FU	
TKHC56H33SH375-MU	TKHC56H33SH375R**
TKHC56H33SH375-FU	
TKHC56H33SH400-MU	TKHC56H33SH400R**
TKHC56H33SH400-FU	

■ ケーブルクランプクシ歯形

形番	適用ブラケット
TKHC56H33SH50-CL-U	TKHC56H33SH50-MU/FU
TKHC56H33SH75-CL-U	TKHC56H33SH75-MU/FU
TKHC56H33SH100-CL-U	TKHC56H33SH100-MU/FU
TKHC56H33SH125-CL-U	TKHC56H33SH125-MU/FU
TKHC56H33SH150-CL-U	TKHC56H33SH150-MU/FU
TKHC56H33SH175-CL-U	TKHC56H33SH175-MU/FU

■ クランプレール（スチール製）

形番	適用ブラケット
TKHC56-〇〇CRA25-10S	TKHC56H33SH**MU/FU

〇〇：50～400 整数

ご注文方法は19ページ

商品質量は231ページ