








CBN インサート ネガティブタイプ

●: 連続加工
●: 軽断続加工
✳: 強断続加工

材料種
インサート
外径用ホルダ
内径用ホルダ
ねじ切り工具
突切り溝入れ
小型旋盤用工具
フライス工具
エンドミル
穴あけ工具
ツリングシステム
ユーザガイド
索引

インサート 形状	形番	寸法 (mm)										ホーニング			アタッシ								
		BXM20	BXC50	BX310	BX330	BX360	BX380	BX480	BX910	BX930	BXC90	コーナ 数	LE	RE		IC	S	D1	標準	シャフト ホーニング	L	H	
		●	✳	●	●	●	●	✳	●	●	●	●	2	2.4		0.4	12.7	4.76	5.16	○		○	
	2QP-SNGA120404	●		●	●	●	●	●	●	●	●	●	2	2.4	0.4	12.7	4.76	5.16	○				
	2QP-SNGA120408	●		●	●	●	●	●	●	●	●	●	2	2.4	0.8	12.7	4.76	5.16	○				
	2QP-SNGA120412	●		●	●	●	●	●	●	●	●	●	2	2.4	1.2	12.7	4.76	5.16	○				
	2QP-SNGA120404-L				●								2	2.4	0.4	12.7	4.76	5.16			○		
	2QP-SNGA120408-L	●			●								2	2.4	0.8	12.7	4.76	5.16			○		
	2QP-SNGA120412-L	●			●								2	2.4	1.2	12.7	4.76	5.16			○		
	2QP-SNGA120404-H					●	●						2	2.4	0.4	12.7	4.76	5.16				○	
	2QP-SNGA120408-H	●				●	●						2	2.4	0.8	12.7	4.76	5.16				○	
	2QP-SNGA120412-H	●				●	●						2	2.4	1.2	12.7	4.76	5.16				○	
	4QP-SNGA120404		●										4	2.4	0.4	12.7	4.76	5.16	○				
	4QP-SNGA120408		●										4	2.4	0.8	12.7	4.76	5.16	○				
	4QP-SNGA120412		●										4	2.4	1.2	12.7	4.76	5.16	○				
	SNGA120402-QBN					●							1	4.1	0.2	12.7	4.76	5.16	○				
	SNGA120404-QBN					●							1	4.1	0.4	12.7	4.76	5.16	○				
	SNGA120408-QBN					●							1	4.1	0.8	12.7	4.76	5.16	○				
	SNGA120412-QBN					●							1	4.1	1.2	12.7	4.76	5.16	○				
	2QP-SNGN090308											●	2	2.4	0.8	9.525	3.18		○				
	2QP-SNGN090312											●	2	2.4	1.2	9.525	3.18		○				
	S-SNGN090308											●	8		0.8	9.525	3.18		○			○	
	S-SNGN090312											●	8		1.2	9.525	3.18		○			○	
	S-SNGN120308											●	8		0.8	12.7	3.18		○			○	
	S-SNGN120312											●	8		1.2	12.7	3.18		○			○	
	S-SNGN120408											●	8		0.8	12.7	4.76		○			○	
	S-SNGN120412										●	8		1.2	12.7	4.76		○			○		

●: 設定アイテム

参照ページ: 外径ホルダ → C091 - 内径ホルダ → D038 - カートリッジ → K197 -