






ひし形穴つき
80° ポジ11°

[illegible]

用途	ブレーカ 記号	形 番	コーティング												コーテッド サーメット	サーメット	超硬	寸法 (mm)						
			T9215	T9225	T6215	T505	T515	T5115	AH8005	AH8015	AH6225	AH6235	AH905	AH725	AH120	GH730	GT9530	AT9530	NS9530	TH10	RE	IC	S	D1
	PS	CPMT060202-PS	●	●	●			●	●	●			●		●		●				0.2	6.35	2.38	2.8
		CPMT060204-PS	●	●	●			●	●	●			●	●	●		●	●	●		0.4	6.35	2.38	2.8
		CPMT060208-PS	●	●	●				●	●							●		●		0.8	6.35	2.38	2.8
		CPMT080202-PS	●	●	●					●	●		●				●	●	●		0.2	7.94	2.38	3.4
		CPMT080204-PS	●	●	●						●	●	●				●	●	●		0.4	7.94	2.38	3.4
		CPMT080208-PS	●	●	●							●	●				●	●	●		0.8	7.94	2.38	3.4
		CPMT090304-PS	●	●	●					●	●		●				●	●	●		0.4	9.525	3.18	4.4
		CPMT090308-PS	●	●	●						●	●	●				●	●	●	●	0.8	9.525	3.18	4.4
		CPMT09T302-PS	●	●	●			●	●	●			●					●			0.2	9.525	3.97	4.4
		CPMT09T304-PS	●	●	●			●	●	●			●					●			0.4	9.525	3.97	4.4
		CPMT09T308-PS	●	●	●			●	●	●			●	●				●			0.8	9.525	3.97	4.4
		TM	CPMT060202-TM	●	●	●				●	●							●			0.2	6.35	2.38	2.8
		CPMT060204-TM	●	●	●					●	●							●			0.4	6.35	2.38	2.8
		CPMT060208-TM	●	●	●						●	●						●			0.8	6.35	2.38	2.8
		CPMT09T302-TM	●	●	●					●	●							●			0.2	9.525	3.97	4.4
		CPMT09T304-TM	●	●	●						●	●						●			0.4	9.525	3.97	4.4
		CPMT09T308-TM	●	●	●					●	●							●			0.8	9.525	3.97	4.4
	CM	CPMT060204-CM						●												0.4	6.35	2.38	2.8	
		CPMT060208-CM						●												0.8	6.35	2.38	2.8	
		CPMT080204-CM						●												0.4	7.94	2.38	3.4	
		CPMT080208-CM						●												0.8	7.94	2.38	3.4	
		CPMT090304-CM				●	●	●												0.4	9.525	3.18	4.4	
		CPMT090308-CM				●	●	●												0.8	9.525	3.18	4.4	
		CPMT09T304-CM				●	●	●												0.4	9.525	3.97	4.4	
		CPMT09T308-CM				●	●	●												0.8	9.525	3.97	4.4	
		CPMT09T312-CM						●												1.2	9.525	3.97	4.4	
		CPMT120408-CM						●												0.8	12.7	4.76	5.5	
全周	CPMT120412-CM						●													1.2	12.7	4.76	5.5	
	CPMT120408						●	●			●									0.8	12.7	4.76	5.5	
																								

切りくず処理範囲



Tungaloy B119