


YW

[illegible]

用途	ブレーカ 記号	形 番	コーティング					コート サメット	サメット	寸法 (mm)					
			T9215	T9225	T6215	AH8015	AH6225	GT9530	NS9530	RE	IC	S	D		
仕 上 げ 中 切 削		ZF YWMT11T202-ZF	●	●	●	●	●	●		0.2	4.679	2.78	2.3		
		YWMT11T204-ZF	●	●	●	●	●	●	●		0.4	4.679	2.78	2.3	
		YWMT16T302-ZF	●	●	●	●	●	●	●		0.2	7.018	3.97	2.8	
		YWMT16T304-ZF	●	●	●	●	●	●	●		0.4	7.018	3.97	2.8	
		YWMT16T308-ZF	●	●	●	●	●	●	●		0.8	7.018	3.97	2.8	
		ZM YWMT11T202-ZM	●	●	●	●	●	●	●		0.2	4.679	2.78	2.3	
		YWMT11T204-ZM	●	●	●	●	●	●	●	●		0.4	4.679	2.78	2.3
		YWMT16T302-ZM	●	●	●	●	●	●	●	●		0.2	7.018	3.97	2.8
		YWMT16T304-ZM	●	●	●	●	●	●	●	●		0.4	7.018	3.97	2.8
		YWMT16T308-ZM	●	●	●	●	●	●	●	●		0.8	7.018	3.97	2.8

JXF

[illegible][illegible]

Tungaloy B159