

インサート ネガティブタイプ


●: 連続加工
●: 弱断続加工
●: 強断続加工

YN



ひし形穴つき
25°

P	鋼	●●●●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
M	ステンレス	●●																				
K	鋳鉄	●●																				
N	非鉄金属																					
S	難削材																					
H	高硬度材																					



用途	ブレーカ 記号	形番	コーティング							サーマット			寸法 (mm)						
			T9215	T9225	T9235	T6215	AH8015	AH6225	GT9530	NS9530	RE	IC	S	D1					
仕上げ切削 ・軟鋼用	ZF	YNMG160404-ZF	●	●	●	★	●	★	●							0.4	9.525	4.76	3.81
		YNMG160408-ZF	●	●	●	★	●	★	●							0.8	9.525	4.76	3.81
中切削 ・軟鋼用	ZM	YNMG160404-ZM	★	●	●	★	●	★	●							0.4	9.525	4.76	3.81
		YNMG160408-ZM	●	●	●	★	●	★	●							0.8	9.525	4.76	3.81


★: 2023 年発売予定
●: 設定アイテム

KN



平行四辺形
穴なし55°

P	鋼	●●																				
M	ステンレス	●●																				
K	鋳鉄	●●																				
N	非鉄金属																					
S	難削材																					
H	高硬度材																					



用途	ブレーカ 記号	形番	コーティング							寸法 (mm)								
			GH330							RE	IC	S	D1					
仕上げ切削	S1	KNMX160405R-S1	●												0.5	9.525	4.76	-
		KNMX160405L-S1	●												0.5	9.525	4.76	-

●: 設定アイテム

切りくず処理範囲

